



Eaton FWA-50A21F

Eaton Bussmann series FWA high speed fuse, 500 Vac/dc (35-800A only), 50A, 100 kAIC, Non Indicating, High speed fuse, Ferrule end X ferrule end

Specifications

PRODUCT NAME	Eaton Bussmann series high speed cylindrical fuse
CATALOG NUMBER	FWA-50A21F
UPC	051712795289
PRODUCT LENGTH/DEPTH	62 mm
PRODUCT HEIGHT	47 mm
PRODUCT WIDTH	110 mm
PRODUCT WEIGHT	56.2 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	CSA Certified UL Recognized

□□□□

□□

AMPERAGE RATING	50 A
BREAKING CAPACITY	200 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
FUSE INDICATOR	Other
RELEASE CHARACTERISTIC	Other
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
FUSE SIZE	21 x 51 mm
RATED VOLTAGE AC	150 V
RATED VOLTAGE DC	150 V
CLASS	Class aR
CLEARING (I2T)	1600 at 150 V
WATT LOSSES	7.3 W
FUSE SHAPE	Cylindrical
PRE ARC (I2T)	170
INTERRUPT RATING	100 kAIC
CONNECTION	Ferrule end x ferrule end
CONSTRUCTION SIZE	Other
MATERIAL	Ceramic
PACKAGING TYPE	Standard
VOLTAGE RATING	150 V
TYPE	High speed fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
FUSE TYPE	FWA-A21F
BREAKING CAPACITY AT NOMINAL VOLTAGE, AC	200 kA
BREAKING CAPACITY AT NOMINAL VOLTAGE, DC	50 kA

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

