

## Eaton EP-501305

EMC2-H26/55-W . Wall-mounted enclosure  
EMC2 empty, IP55, protection class II,  
HxWxD=950x550x270mm, white (RAL 9016)

<b>PRODUCT NAME</b>	Eaton xEnergy Basic EMC2 enclosure wall-mounted
<b>CATALOG NUMBER</b>	EP-501305
<b>PRODUCT LENGTH/DEPTH</b>	270 mm
<b>PRODUCT HEIGHT</b>	950 mm
<b>PRODUCT WIDTH</b>	550 mm
<b>PRODUCT WEIGHT</b>	24 kg
<b>CERTIFICATIONS</b>	CE



<b>FEATURES</b>	EMC-version Connectable
<b>FITTED WITH:</b>	Door
<b>SURFACE FINISHING</b>	Powder coating
<b>DEGREE OF PROTECTION</b>	IP55 IK10 Other
<b>MATERIAL QUALITY</b>	Other
<b>COLOR</b>	White
<b>PERMISSIBLE LOAD OF THE MOUNTING PLATE ACCORDING TO IEC 62208 - MAX</b>	480 N
<b>NUMBER OF LOCKS</b>	0
<b>RAL-NUMBER</b>	9016
<b>MATERIAL</b>	Steel
<b>MOUNTING METHOD</b>	Wall mounting
<b>INSTALLATION TYPE</b>	Floor standing wall model
<b>NUMBER OF COVERS/DOORS</b>	1
<b>PERMISSIBLE LOAD OF THE ENCLOSURE ACCORDING TO IEC 62208 - MAX</b>	2000 N
<b>PERMISSIBLE LOAD OF THE DOOR(S) ACCORDING TO IEC 62208 - MAX</b>	100 N
<b>THERMAL DISSIPATION (DELTA T = 20 K) ACCORDING TO IEC/TR 60890</b>	72 W
<b>NUMBER OF CONNECTOR HOLES</b>	0



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

