

## Eaton FWC-20A10F

Eaton Bussmann series FWC high speed cylindrical fuse, 500V, 20A, 200 kAIC Vac, 50 kAIC at 700 Vdc, Non Indicating, High speed fuse, Ferrule end X ferrule end

PRODUCT NAME	Eaton Bussmann series high speed cylindrical fuse
CATALOG NUMBER	FWC-20A10F
UPC	051712796460
PRODUCT LENGTH/DEPTH	38 mm
PRODUCT HEIGHT	11 mm
PRODUCT WIDTH	11 mm
PRODUCT WEIGHT	8.8 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	CSA Certified UL Recognized

AMPERAGE RATING	20 A
ACCESSORIES	<ul style="list-style-type: none"> <li>• BMM Fuse block</li> <li>• CHM modular fuse holder</li> </ul>
BREAKING CAPACITY	200 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
FUSE INDICATOR	Other
RELEASE CHARACTERISTIC	Other
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
FUSE SIZE	10 x 38 mm
RATED VOLTAGE AC	600 V
RATED VOLTAGE DC	700 V
CLASS	Class aR
CLEARING (I2T)	260
WATT LOSSES	4.8 W
FUSE SHAPE	Cylindrical
PRE ARC (I2T)	34
INTERRUPT RATING	200 kAIC Vac
CONNECTION	Ferrule end x ferrule end
CONSTRUCTION SIZE	10 x 38 mm 10 mm x 38 mm
MATERIAL	Ceramic
PACKAGING TYPE	Standard
VOLTAGE RATING	600 V
TYPE	High speed fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
FUSE TYPE	FWC-A10F
BREAKING CAPACITY AT NOMINAL VOLTAGE, AC	200 kA
BREAKING CAPACITY AT NOMINAL VOLTAGE, DC	10 kA

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

