



□□□□□

Eaton FWH-20A14F

Eaton Bussmann series FWH high speed fuse, 1000 Vac, 800 Vdc, 20A, 200 kAIC Vac, 50 kAIC at 500 Vdc, Non Indicating, High speed fuse, Ferrule end X ferrule end

□□□□

PRODUCT NAME	Eaton Bussmann series high speed cylindrical fuse
CATALOG NUMBER	FWH-20A14F
UPC	051712370820
PRODUCT LENGTH/DEPTH	51 mm
PRODUCT HEIGHT	15 mm
PRODUCT WIDTH	15 mm
PRODUCT WEIGHT	21.2 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized CSA Certified

AMPERAGE RATING 20 A

ACCESSORIES

- CH14 Modular fuse holder
- FW14-PCB

BREAKING CAPACITY 200 kA

FREQUENCY RATING - MAX 62 Hz

FREQUENCY RATING - MIN 45 Hz

FUSE INDICATOR Other

RELEASE CHARACTERISTIC Other

UTILIZATION CATEGORY aR (accompanied semiconductor protection)

VOLTAGE TYPE AC/DC

FUSE SIZE 14 x 51 mm

RATED VOLTAGE AC 500 V

CLASS Class aR

CLEARING (I₂T) 96 at 500 V

WATT LOSSES 6 W

FUSE SHAPE Cylindrical

PRE ARC (I₂T) 26

INTERRUPT RATING 50 kAIC

CONNECTION Ferrule end x ferrule end

CONSTRUCTION SIZE 14 mm x 51 mm

MATERIAL Ceramic

PACKAGING TYPE Standard

VOLTAGE RATING 600 V

TYPE High speed fuse

APPLICATION Semiconductor, DC
Common bus, DC drives,
Power converters/rectifiers

FUSE TYPE FWH-A14F

BREAKING CAPACITY AT NOMINAL VOLTAGE, AC 50 kA

DECLARATIONS OF
CONFORMITY

[eaton-high-speed-cylindrical-fuse-declaration-of-conformity-uk250904en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

