



Eaton F1340

Eaton Moeller series Ceiling Range (CIRCA) - Wiring Devices. Ceiling pull switch, 50A, 2p, c/w neon and flag indicator

□□□□

PRODUCT NAME	Eaton Moeller series Ceiling Range (CIRCA) - Wiring devices
CATALOG NUMBER	F1340
PRODUCT LENGTH/DEPTH	90 mm
PRODUCT HEIGHT	86 mm
PRODUCT WIDTH	86 mm
PRODUCT WEIGHT	0.199 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	BS EN 60669-1 IEC 60669-1



Powering Business Worldwide

□□□□

FEATURES	Halogen free
SURFACE FINISHING	Matt
SPECIAL FEATURES	Terminal Screw Zinc Coated Steel with clear Passivation
TYPE	<ul style="list-style-type: none"> • Ceiling switches and accessories • Circa ceiling accessory
AMPERAGE RATING	50 A
VOLTAGE RATING	250 V AC
CONTACT MATERIAL	Silver Nickel
HEAD STYLE	Combination head
ILLUMINATION	No
SURFACE PROTECTION	Untreated
MATERIAL QUALITY	Thermoplastic
ASSEMBLY ARRANGEMENT	Basic element with complete housing
BASE COLOR	Gray
BASE MATERIAL	Thermoplastic
TERMINAL MATERIAL	Brass
BUILT-IN DEPTH	0 mm
BUILT-IN INSTALLATION BOX DEPTH - MIN	45 mm
NOMINAL VOLTAGE - MAX	250 V
NUMBER OF MODULES (MODULE SYSTEM)	0
NUMBER OF ROCKERS	1
SWITCH TYPE	Double pole
MOUNTING METHOD	Surface mounted (plaster)
DEGREE OF PROTECTION	IP20
FASTENING TYPE	Screw mounting
NUMBER OF GANGS	1
FIXING CENTERS	60.3 mm
FRONT PLATE COLOR/FINISHING	White
MATERIAL	Plastic
FRONT PLATE DEPTH	9 mm
FRONT PLATE MATERIAL	Urea
FRONT PLATE/MODULE DIMENSIONS	86 mm x 86 mm

□□

□□□□

[eaton-us-power-defense-flyer-br013004en-en-us.pdf](#)

WIRING SYSTEM	2-pole switch
METHOD OF OPERATION	Pull cord
FUNCTION LIGHTING	Other
COLOR	White
TERMINAL CAPACITY (LN AND E)	4 mm ² (3x) or 6 mm ² (2x) or 10 mm ² (1x)
CONNECTION TYPE	Screw terminal
LABEL SPACE/INFORMATION SURFACE	No
LIGHTING TYPE	Other
RAL-NUMBER (AKIN)	9016
RECOMMENDED BACK BOX DEPTH - MIN	45 mm
SWITCHING CURRENT OF FLUORESCENT LAMPS	45 Ampere AC/DC

□□□□:
□□□□:
□□□:
□□:



□□□□ Eaton House
 30 Pembroke Road
 Dublin 4, □□□□
 Eaton.com

