



Eaton FD630

Eaton Bussmann series low voltage british standard fuse, 630A, AC 415 V, DC 250 V, 74 x 135 mm, gL/gG

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	FD630
PRODUCT LENGTH/DEPTH	73.3 mm
PRODUCT HEIGHT	73.3 mm
PRODUCT WIDTH	134.5 mm
PRODUCT WEIGHT	894 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	BS88 IEC 60269 EAC

□□□□

□□

AMPERAGE RATING	630 A
CURRENT TYPE	AC/DC
MOUNTING DIMENSION	M10
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	110 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	415 V
RATED VOLTAGE DC	250 V
CLASS	Class gG/gL
FUSE TYPE	FD
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
CONNECTION	Bolt-on
CONSTRUCTION SIZE	Other
FUSE SHAPE	Center bolted tags
VOLTAGE TYPE	AC/DC
VOLTAGE RATING	415 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

