

Eaton FF500

Eaton Bussmann series low voltage british standard fuse, 500A, AC 690 V, V88/C2, 74 x 210 mm, gL/gG

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	FF500
UPC	051712839907
PRODUCT LENGTH/DEPTH	209 mm
PRODUCT HEIGHT	74 mm
PRODUCT WIDTH	74 mm
PRODUCT WEIGHT	1034 g
COMPLIANCES	RoHS Compliant

AMPERAGE RATING	500 A
FITTED WITH:	Centre bolted tags
FUSE SIZE	BS88/C2
CURRENT TYPE	AC/DC
MOUNTING DIMENSION	M10
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	185 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	690 V
RATED VOLTAGE DC	400 V
CLASS	Class gG/gL
FUSE TYPE	FF
UTILIZATION CATEGORY	gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	38 W
CONNECTION	133/184 mm fixing centre
CONSTRUCTION	BS88/C2
CONSTRUCTION SIZE	C2
FUSE SHAPE	Center bolted tags
VOLTAGE TYPE	AC/DC
VOLTAGE RATING	690 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-
standard-fuse-declaration-
of-conformity-
uk250892en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

