



□□□□□

Eaton FG630

Eaton Bussmann series low voltage british standard fuse, 630A, AC 415 V, 74 x 262 mm, gL/gG

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	FG630
UPC	051712844949
PRODUCT LENGTH/DEPTH	263 mm
PRODUCT HEIGHT	74 mm
PRODUCT WIDTH	74 mm
PRODUCT WEIGHT	1275 g
COMPLIANCES	RoHS Compliant

□□□□

AMPERAGE RATING	630 A
FITTED WITH:	Centre bolted tags
CURRENT TYPE	AC/DC
MOUNTING DIMENSION	M10
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	231 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	415 V
RATED VOLTAGE DC	400 V
CLASS	Class gG/gL
FUSE TYPE	FG
UTILIZATION CATEGORY	gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	50 W
CONNECTION	167/231 mm fixing centre
CONSTRUCTION	BS88
CONSTRUCTION SIZE	Other
FUSE SHAPE	Center bolted tags
VOLTAGE TYPE	AC/DC
VOLTAGE RATING	415 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

□□

DECLARATIONS OF
CONFORMITY

[eaton-low-voltage-british-
standard-fuse-declaration-
of-conformity-
uk250892en.pdf](#)

