



□□□□

Eaton FT1EW4ICGS

EATON FlexiTech, Exit sign, wall, 12m, 4
picto. (DRLU), CG-S

□□□□

PRODUCT NAME	Eaton FlexiTech EW CBS exit sign
CATALOG NUMBER	FT1EW4ICGS
PRODUCT LENGTH/DEPTH	231 mm
PRODUCT HEIGHT	34 mm
PRODUCT WIDTH	86 mm
PRODUCT WEIGHT	0.32 kg
CERTIFICATIONS	CE



Powering Business Worldwide



BATTERY QUALITY	Not applicable
GLOW WIRE TEST	850 °C
PERMISSIBLE AMBIENT TEMPERATURE - MIN	-20 °C
PERMISSIBLE AMBIENT TEMPERATURE - MAX	40 °C
PROTECTION CLASS	II
OUTDOOR USE COMPLIANCE	False
EXPLOSION PROTECTED	False
DEGREE OF PROTECTION	IP43
MODE	Maintained / Non-Maintained (M / NM)
LAMP TYPE	LED not exchangeable
WITH LIGHT SOURCE	True
LAMP HOLDER	None
TYPE OF INDICATOR	Only single-sided
MONITORING EQUIPMENT	None
POWER SUPPLY SYSTEM	Central (central battery)
VOLTAGE TYPE	AC/DC
CURRENT CONSUMPTION AT 220V DC	3.9 mA
APPARENT POWER AT MAINS OPERATION	3 VA
POWER FACTOR	0.33
RESERVE-POLARITY PROTECTED	True
ENERGY EFFICIENCY CLASS	A
CONDUCTOR CROSS SECTION	2.5
CONNECTION TYPE	Plug-in connection
MAX. SYSTEM POWER	1 W
NOMINAL VOLTAGE AC - MAX	230 V
RATED AMBIENT TEMP ACC. IEC62722-2-1 - MIN	5 °C
RATED AMBIENT TEMP ACC. IEC62722-2-1 - MAX	35 °C
INRUSH CURRENT	<=1,5A
SUITABLE FOR STANDBY SWITCHING	No
SUITABLE FOR CONTINUOUS CIRCUIT	No



RAL-NUMBER (SIMILAR) HOUSING	9003
MOUNTING METHOD	Wall surface mounted
MATERIAL HOUSING	Plastic
COLOR HOUSING	White
MATERIAL COVER	Plastic, transparent
LABELLING TYPE	Insert sheet/plate
PICTOGRAM INCLUDED	True
BUILT-IN LENGTH	252 mm
BUILT-IN WIDTH	102 mm
BUILT-IN HEIGHT/DEPTH	50 mm
NUMBER OF POLES (NUMERIC)	3
IMPACT STRENGTH	IK07
KIND OF LUMINAIRE	Exit sign luminaire
COLOR TEMPERATURE - MAX	6500 K
COLOR TEMPERATURE - MIN	6500 K
LIGHT DISTRIBUTOR	Diffuser lens/optic/panel
ENERGY EFFICIENCY CLASS OF THE BUILT-IN LAMP	A++, A+, A (LED)
FUNCTION	Escape route signage
COLOR OF LIGHT	White
COLOR RENDERING INDEX (CRI)	80
LUMINAIRE WITH LIMITED SURFACE TEMPERATURE, SIGN D	False
NUMBER OF LIGHTING HEADS	1
SUITABLE FOR NUMBER OF LAMPS	1
VIEWING DISTANCE	12 m
DATA CONNECTION TERMINAL	0.5-2.5 mm ²
FREQUENCY	50/60 Hz
MAIN CONNECTION TERMINAL	0.5-2.5 mm ²
PRODUCT BRANDING	Eaton
NUMBER OF LEDS	16
SHAPE	Rectangular
TOTAL LENGTH	231 mm
APPLICATION	Acc. EN 1838
TESTING SYSTEM	CG technology

