

Eaton FWP-10G14FI

Eaton Bussmann series FWP high speed fuse, 690V, 10A, 200 kAIC, With Indicator, High speed fuse, Ferrule end X ferrule end

PRODUCT NAME	Eaton Bussmann series high speed cylindrical fuse
CATALOG NUMBER	FWP-10G14FI
UPC	051712689564
PRODUCT LENGTH/DEPTH	51 mm
PRODUCT HEIGHT	14 mm
PRODUCT WIDTH	14 mm
PRODUCT WEIGHT	19.8 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized IEC Rated

AMPERAGE RATING	10 A
ACCESSORIES	<ul style="list-style-type: none"> • CH14 Modular fuse holder • FW14-PCB
BREAKING CAPACITY	200 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
FUSE INDICATOR	Top fuse status indicator
RELEASE CHARACTERISTIC	Other
UTILIZATION CATEGORY	gR (general purpose semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	14 x 51 mm
RATED VOLTAGE AC	690 V
CLASS	Class gR
CLEARING (I ² T)	47
WATT LOSSES	2.52 W
FUSE SHAPE	Cylindrical
PRE ARC (I ² T)	5.9
INTERRUPT RATING	200 kAIC
FITTED WITH:	Striker
CONNECTION	Ferrule end x ferrule end
CONSTRUCTION SIZE	14 mm x 51 mm
MATERIAL	Ceramic
PACKAGING TYPE	Standard
VOLTAGE RATING	500 V
TYPE	High speed fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
FUSE TYPE	FWP-G14FI
BREAKING CAPACITY AT NOMINAL VOLTAGE, AC	200 kA



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

