



□□□□

Eaton FWP-15B

Eaton Bussmann series FWP high speed fuse, 700 Vac (UL), 690 Vac (IEC), 500 Vdc (2-100A), 500 Vac, 15A, 200 kAIC Vac, 50 kAIC at 700 Vdc, None, High speed fuse, Blade end X blade end, Stud

□□□□

PRODUCT NAME	Eaton Bussmann series high speed cylindrical fuse
CATALOG NUMBER	FWP-15B
UPC	051712557801
PRODUCT LENGTH/DEPTH	73 mm
PRODUCT HEIGHT	15 mm
PRODUCT WIDTH	15 mm
PRODUCT WEIGHT	25.3 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized CSA Certified



Powering Business Worldwide



AMPERAGE RATING	15 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Non Indicating
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
FUSE SIZE	14 x 51 mm
RATED SWITCHING CAPACITY	200 A
RATED VOLTAGE AC	700 V
RATED VOLTAGE DC	700 V
MOUNTING DIMENSION	M6
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	63.35 mm
CURRENT TYPE	AC/DC
CLASS	Class aR
CLEARING (I²T)	75 at 700 V
WATT LOSSES	5.5 W
FUSE SHAPE	Center bolted tags
PRE ARC (I²T)	10
COLOR	None
INTERRUPT RATING	200 kAIC Vac 50 kAIC at 700 Vdc 200 kAIC at 300 Vdc 50 kAIC at 300 Vdc
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Stud
PACKAGING TYPE	Standard
VOLTAGE RATING	700 Vac, 700 Vdc (UL)
TYPE	High speed fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
FUSE TYPE	FWP-B
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

