

## Eaton FWA-5A10F

Eaton Bussmann series FWA high speed fuse, 500 Vac/dc (35-800A only), 5A, 100 kAIC, Non Indicating, High speed fuse, Ferrule end X ferrule end

PRODUCT NAME	Eaton Bussmann series high speed cylindrical fuse
CATALOG NUMBER	FWA-5A10F
UPC	051712795197
PRODUCT LENGTH/DEPTH	39 mm
PRODUCT HEIGHT	11 mm
PRODUCT WIDTH	11 mm
PRODUCT WEIGHT	9.2 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized CSA Certified



AMPERAGE RATING	5 A
ACCESSORIES	<ul style="list-style-type: none"><li>• BMM Fuse block</li><li>• CHM modular fuse holder</li></ul>
BREAKING CAPACITY	200 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
FUSE INDICATOR	Other
RELEASE CHARACTERISTIC	Other
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
FUSE SIZE	10 x 38 mm
RATED VOLTAGE AC	150 V
RATED VOLTAGE DC	150 V
CLASS	Class aR
CLEARING (I2T)	8
WATT LOSSES	2 W
FUSE SHAPE	Cylindrical
PRE ARC (I2T)	1.6
INTERRUPT RATING	100 kAIC
CONNECTION	Ferrule end x ferrule end
CONSTRUCTION SIZE	10 x 38 mm 10 mm x 38 mm
MATERIAL	Ceramic
PACKAGING TYPE	Standard
VOLTAGE RATING	150 V
TYPE	High speed fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
FUSE TYPE	FWA-A10F
BREAKING CAPACITY AT NOMINAL VOLTAGE, AC	200 kA
BREAKING CAPACITY AT NOMINAL VOLTAGE, DC	50 kA

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

