



## Eaton FWP-20A22F

Eaton Bussmann series FWP high speed fuse, 700 Vac, 700 Vdc, 20A, 200 kAIC at 300 Vdc, 50 kAIC at 300 Vdc, Non Indicating, High speed fuse, Ferrule end X ferrule end, Class aR, White, Ceramic

### □□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series high speed cylindrical fuse
<b>CATALOG NUMBER</b>	FWP-20A22F
<b>UPC</b>	051712796521
<b>PRODUCT LENGTH/DEPTH</b>	56 mm
<b>PRODUCT HEIGHT</b>	23 mm
<b>PRODUCT WIDTH</b>	23 mm
<b>PRODUCT WEIGHT</b>	55.7 g
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	UL Recognized CSA Certified

□□□□

<b>USED WITH</b>	Finger safe holders/blocks and striker
<b>AMPERAGE RATING</b>	20 A
<b>ACCESSORIES</b>	JM70100 Fuse base
<b>BREAKING CAPACITY</b>	200 kA
<b>FREQUENCY RATING - MAX</b>	62 Hz
<b>FREQUENCY RATING - MIN</b>	45 Hz
<b>FUSE INDICATOR</b>	Other
<b>RELEASE CHARACTERISTIC</b>	Other
<b>UTILIZATION CATEGORY</b>	aR (accompanied semiconductor protection)
<b>VOLTAGE TYPE</b>	AC/DC
<b>FUSE SIZE</b>	22 x 58 mm
<b>RATED VOLTAGE AC</b>	700 V
<b>RATED VOLTAGE DC</b>	700 V
<b>CLASS</b>	Class aR
<b>CLEARING (I<sup>2</sup>T)</b>	330
<b>WATT LOSSES</b>	5 W
<b>FUSE SHAPE</b>	Cylindrical
<b>MINIMUM MELTING</b>	19 I <sup>2</sup> t (A <sup>2</sup> sec)
<b>PRE ARC (I<sup>2</sup>T)</b>	23
<b>COLOR</b>	White
<b>INTERRUPT RATING</b>	200 kAIC
<b>CONNECTION</b>	Ferrule end x ferrule end
<b>CONSTRUCTION SIZE</b>	22 mm x 58 mm
<b>MATERIAL</b>	Ceramic
<b>PACKAGING TYPE</b>	Standard
<b>QUANTITY</b>	10
<b>VOLTAGE RATING</b>	700 V
<b>TYPE</b>	High speed fuse
<b>APPLICATION</b>	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
<b>FUSE TYPE</b>	FWP-A22F
<b>BREAKING CAPACITY AT NOMINAL VOLTAGE, AC</b>	200 kA
<b>BREAKING CAPACITY AT NOMINAL VOLTAGE, DC</b>	50 kA

□□

DECLARATIONS OF  
CONFORMITY

[eaton-high-speed-cylindrical-fuse-declaration-of-conformity-uk250879en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

