

## Eaton FWC-3A10F

Eaton Bussmann series FWC high speed cylindrical fuse, 500 Vac/dc (35-800A only), 3A, Non Indicating, High speed fuse, Cylindrical

PRODUCT NAME	Eaton Bussmann series high speed cylindrical fuse
CATALOG NUMBER	FWC-3A10F
UPC	051712246033
PRODUCT LENGTH/DEPTH	44 mm
PRODUCT HEIGHT	23 mm
PRODUCT WIDTH	54 mm
PRODUCT WEIGHT	8.8 g
COMPLIANCES	RoHS Compliant



AMPERAGE RATING	3 A
ACCESSORIES	<ul style="list-style-type: none"><li>• BMM Fuse block</li><li>• CHM modular fuse holder</li></ul>
BREAKING CAPACITY	200 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
FUSE INDICATOR	Other
RELEASE CHARACTERISTIC	Other
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
FUSE SIZE	10 x 38 mm
RATED VOLTAGE AC	600 V
RATED VOLTAGE DC	700 V
CLASS	Class aR
CLEARING (I2T)	11
WATT LOSSES	1.5 W
CONSTRUCTION TYPE	Ceramic tube
FUSE SHAPE	Cylindrical
PRE ARC (I2T)	1.6
INTERRUPT RATING	200 kAIC
CONSTRUCTION SIZE	10 x 38 mm 10 mm x 38 mm
MATERIAL	Ceramic
MOUNTING METHOD	Cylindrical
PACKAGING TYPE	Standard
QUANTITY	10
VOLTAGE RATING	600 V
TYPE	High speed fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
FUSE TYPE	FWC-A10F
BREAKING CAPACITY AT NOMINAL VOLTAGE, AC	200 kA
BREAKING CAPACITY AT NOMINAL VOLTAGE, DC	10 kA



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com  
© 2025

Follow us on social media to get the latest product and support information.

