

Eaton FWP-32A22F

Eaton Bussmann series FWP high speed fuse, 700 Vac (IEC), 700 Vdc (UL), 32A, 200 kAIC at 300 Vdc, 50 kAIC at 300 Vdc, Non Indicating, High speed fuse, Ferrule end X ferrule end, Class aR, White, Ceramic

PRODUCT NAME	Eaton Bussmann series high speed cylindrical fuse
CATALOG NUMBER	FWP-32A22F
UPC	051712796545
PRODUCT LENGTH/DEPTH	58 mm
PRODUCT HEIGHT	23 mm
PRODUCT WIDTH	23 mm
PRODUCT WEIGHT	63.1 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	CSA Certified UL Recognized

USED WITH	Finger safe holders/blocks and striker
AMPERAGE RATING	32 A
ACCESSORIES	JM70100 Fuse base
BREAKING CAPACITY	200 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
FUSE INDICATOR	Other
RELEASE CHARACTERISTIC	Other
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
FUSE SIZE	22 x 58 mm
RATED VOLTAGE AC	700 V
RATED VOLTAGE DC	700 V
CLASS	Class aR
CLEARING (I2T)	780
WATT LOSSES	8 W
FUSE SHAPE	Cylindrical
MINIMUM MELTING	53.5 I2t (A2 sec)
PRE ARC (I2T)	55
COLOR	White
INTERRUPT RATING	200 kAIC
CONNECTION	Ferrule end x ferrule end
CONSTRUCTION SIZE	22 mm x 58 mm
MATERIAL	Ceramic
PACKAGING TYPE	Standard
QUANTITY	10
VOLTAGE RATING	700 V
TYPE	High speed fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
FUSE TYPE	FWP-A22F
BREAKING CAPACITY AT NOMINAL VOLTAGE, AC	200 kA
BREAKING CAPACITY AT NOMINAL VOLTAGE, DC	50 kA

DECLARATIONS OF CONFORMITY

[eaton-high-speed-cylindrical-fuse-declaration-of-conformity-uk250879en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

