



## Eaton FWP-20G14F

Eaton Bussmann series FWP high speed fuse, 690 V, 20A, 200 kAIC, Non Indicating, High speed fuse, Ferrule end X ferrule end

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series high speed cylindrical fuse
<b>CATALOG NUMBER</b>	FWP-20G14F
<b>UPC</b>	051712689502
<b>PRODUCT LENGTH/DEPTH</b>	51 mm
<b>PRODUCT HEIGHT</b>	14 mm
<b>PRODUCT WIDTH</b>	14 mm
<b>PRODUCT WEIGHT</b>	19 g
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	UL Recognized IEC Rated

□□□□

**AMPERAGE RATING** 20 A

**ACCESSORIES**

- CH14 Modular fuse holder
- FW14-PCB

**BREAKING CAPACITY** 200 kA

**FREQUENCY RATING - MAX** 62 Hz

**FREQUENCY RATING - MIN** 45 Hz

**FUSE INDICATOR** Non Indicating

**RELEASE CHARACTERISTIC** Other

**UTILIZATION CATEGORY** gR (general purpose semiconductor protection)

**VOLTAGE TYPE** AC

**FUSE SIZE** 14 x 51 mm

**RATED VOLTAGE AC** 690 V

**CLASS** Class gR

**CLEARING (I<sub>2</sub>T)** 170

**WATT LOSSES** 5.4 W

**FUSE SHAPE** Cylindrical

**PRE ARC (I<sub>2</sub>T)** 27

**INTERRUPT RATING** 200 kAIC

**CONNECTION** Ferrule end x ferrule end

**CONSTRUCTION SIZE** 14 mm x 51 mm

**MATERIAL** Ceramic

**PACKAGING TYPE** Standard

**VOLTAGE RATING** 500 V

**TYPE** High speed fuse

**APPLICATION** Semiconductor, DC Common bus, DC drives, Power converters/rectifiers

**FUSE TYPE** FWP-G14F

**BREAKING CAPACITY AT NOMINAL VOLTAGE, AC** 200 kA

□□

DECLARATIONS OF CONFORMITY

[eaton-high-speed-cylindrical-fuse-declaration-of-conformity-uk250950en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

