



Eaton FWP-6G14F

Eaton Bussmann series high speed cylindrical fuse, 690 V, 6 A, 200 kAIC, 14 x 51 mm, Non Indicating, Ferrule end x ferrule end

0000

PRODUCT NAME	Eaton Bussmann series high speed cylindrical fuse
CATALOG NUMBER	FWP-6G14F
UPC	051712689458
PRODUCT LENGTH/DEPTH	51 mm
PRODUCT HEIGHT	14 mm
PRODUCT WIDTH	14 mm
PRODUCT WEIGHT	19 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized IEC Rated

□□□

AMPERAGE RATING	6 A
ACCESSORIES	<ul style="list-style-type: none">• CH14 Modular fuse holder• FW14-PCB
BREAKING CAPACITY	200 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
FUSE INDICATOR	Non Indicating
RELEASE CHARACTERISTIC	Other
UTILIZATION CATEGORY	gR (general purpose semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	14 x 51 mm
RATED VOLTAGE AC	690 V
CLASS	Class gR
CLEARING (I₂T)	48
WATT LOSSES	4.2 W
FUSE SHAPE	Cylindrical
PRE ARC (I₂T)	16
INTERRUPT RATING	200 kAIC
CONNECTION	Ferrule end x ferrule end
CONSTRUCTION SIZE	14 mm x 51 mm
MATERIAL	Ceramic
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V
TYPE	High speed fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
FUSE TYPE	FWP-G14F
BREAKING CAPACITY AT NOMINAL VOLTAGE, AC	200 kA

□□

DECLARATIONS OF CONFORMITY

eaton-high-speed-cylindrical-fuse-declaration-of-conformity-uk250950en.pdf

□□□□:

□□□□:

三三三：

111

EATON
Powering Business Worldwide

□□□□ Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

© 2025 00 0000000

