



□□□□□

Eaton

GHG9601955R0021

Eaton Crouse-Hinds series Ex-e cable gland,
Non-armoured cable, Non-armoured gland,
Polyamide 6, Increased safety, M12, Long
thread

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series Ex-e cable gland
CATALOG NUMBER	GHG9601955R0021
PRODUCT LENGTH/DEPTH	31.3 mm
PRODUCT HEIGHT	15 mm
PRODUCT WIDTH	15 mm
PRODUCT WEIGHT	0.01 kg

Certifications and compliances	
AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	IECEX/ATEX
INGRESS PROTECTION (IP) RATINGS	IP66 IP68

Product specifications	
PROTECTION TYPE	Increased safety
CABLE TYPE	Non-armored Non-armoured
GLAND TYPE	Non-armoured
TYPE	Long thread
THREAD SIZE	M12
THREAD TYPE	Metric
MATERIAL	Polyamide 6

Links	
Documents	Eaton Specification Sheet - GHG9601955R0021
Resources	Crouse-Hinds series CEAG GHG Non-metallic EX Cable Glands catalog page for North American applications
	CEAG GHG Non-metallic Ex Cable Glands EU Type Examination Certificate
Enlargement	Enlargement Gland Sizes M12 and M16 ATEX Certification
	Enlargement Gland IECEx Certificate of Conformity

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	