



Eaton FWP-25B

Eaton Bussmann series FWP high speed fuse, 700 Vac/dc, 25A, 200 kAIC Vac, 50 kAIC at 700 Vdc, None, High speed fuse, Blade end X blade end, Stud

□□□□

PRODUCT NAME	Eaton Bussmann series high speed cylindrical fuse
CATALOG NUMBER	FWP-25B
UPC	051712557825
PRODUCT LENGTH/DEPTH	73 mm
PRODUCT HEIGHT	15 mm
PRODUCT WIDTH	15 mm
PRODUCT WEIGHT	25.4 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized CSA Certified

AMPERAGE RATING	25 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Non Indicating
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
FUSE SIZE	22 x 58 mm
RATED SWITCHING CAPACITY	200 A
RATED VOLTAGE AC	700 V
RATED VOLTAGE DC	700 V
MOUNTING DIMENSION	M6
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	63.35 mm
CURRENT TYPE	AC/DC
CLASS	Class aR
CLEARING (I ² T)	340 at 700 V
WATT LOSSES	7 W
FUSE SHAPE	Center bolted tags
PRE ARC (I ² T)	44
COLOR	None
INTERRUPT RATING	50 kAIC at 700 Vdc 200 kAIC Vac 200 kAIC at 300 Vdc 50 kAIC at 300 Vdc
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Stud
PACKAGING TYPE	Standard
VOLTAGE RATING	700 Vac, 700 Vdc (UL)
TYPE	High speed fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
FUSE TYPE	FWP-B
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

