



Eaton GSGB110

Fuse-link, high speed, 110 A, AC 660 V, DC 400 V, BS88, 36 x 95 mm, aR, BS, Ultra fast



PRODUCT NAME	Eaton Bussmann series high speed british standard fuse
CATALOG NUMBER	GSGB110
UPC	051712392242
PRODUCT LENGTH/DEPTH	210 mm
PRODUCT HEIGHT	42 mm
PRODUCT WIDTH	105 mm
PRODUCT WEIGHT	81.1 g
COMPLIANCES	CE Marked
CERTIFICATIONS	UL Recognized



Powering Business Worldwide

□□□□

□□

AMPERAGE RATING	110 A
BREAKING CAPACITY	100 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
RATED SWITCHING CAPACITY	100 kA
RATED VOLTAGE AC	660 V
RATED VOLTAGE DC	400 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	72 mm
MOUNTING DIMENSION	M8
CURRENT TYPE	AC/DC
CLASS	Class aR
WATT LOSSES	30 W
FUSE SHAPE	Offset dual barrel bolted tags
COLOR	None
CONSTRUCTION SIZE	Other
PACKAGING TYPE	Standard
VOLTAGE RATING	660 V
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	GSG
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

