



Eaton FWP-32G22FI

Eaton Bussmann series high speed cylindrical fuse, 690 V, 32 A, 200 kAIC, 22 x 58 mm, with indicator, Ferrule end x ferrule end, with Striker

□□□□

PRODUCT NAME	Eaton Bussmann series high speed cylindrical fuse
CATALOG NUMBER	FWP-32G22FI
UPC	051712689748
PRODUCT LENGTH/DEPTH	58 mm
PRODUCT HEIGHT	22 mm
PRODUCT WIDTH	22 mm
PRODUCT WEIGHT	52.9 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized IEC Rated

AMPERAGE RATING	32 A
ACCESSORIES	CH22 Modular fuse holder
BREAKING CAPACITY	200 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
FUSE INDICATOR	Top fuse status indicator
RELEASE CHARACTERISTIC	Other
UTILIZATION CATEGORY	gR (general purpose semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	22 x 58 mm
RATED VOLTAGE AC	690 V
CLASS	Class gR
CLEARING (I2T)	616
WATT LOSSES	9.21 W
FUSE SHAPE	Cylindrical
PRE ARC (I2T)	97
INTERRUPT RATING	200 kAIC
FITTED WITH:	Striker
CONNECTION	Ferrule end x ferrule end
CONSTRUCTION SIZE	22 mm x 58 mm
MATERIAL	Ceramic
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V
TYPE	High speed fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
FUSE TYPE	FWP-G22FI
BREAKING CAPACITY AT NOMINAL VOLTAGE, AC	200 kA
BREAKING CAPACITY AT NOMINAL VOLTAGE, DC	50 kA

DECLARATIONS OF CONFORMITY

[eaton-high-speed-cylindrical-fuse-declaration-of-conformity-uk250950en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

