



Eaton GSGB175

Fuse-link, high speed, 175 A, AC 660 V, DC 350 V, BS88, 78 x 107 mm, aR, BS

□□□□

PRODUCT NAME	Eaton Bussmann series high speed british standard fuse
CATALOG NUMBER	GSGB175
PRODUCT LENGTH/DEPTH	107 mm
PRODUCT HEIGHT	78 mm
PRODUCT WIDTH	35 mm
PRODUCT WEIGHT	397.2 g
COMPLIANCES	CE

□□□□

□□

AMPERAGE RATING	175 A
BREAKING CAPACITY	100 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
RATED SWITCHING CAPACITY	100 kA
RATED VOLTAGE AC	660 V
RATED VOLTAGE DC	350 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	81.7 mm
MOUNTING DIMENSION	M10
CURRENT TYPE	AC/DC
CLASS	Class aR
WATT LOSSES	41 W
FUSE SHAPE	Offset bolted tags
COLOR	None
CONSTRUCTION SIZE	Other
VOLTAGE RATING	660 V
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	GSG
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

