



## Eaton FWP-50A14F

Eaton Bussmann series FWP high speed fuse, 700 Vac (UL), 700 Vdc (UL), 690 Vac (IEC), 50A, 200 kAIC at 700 Vac, 50 kAIC at 700 Vdc, Non Indicating, High speed fuse, Ferrule end X ferrule end, Class aR, White, Ceramic

### □□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series high speed cylindrical fuse
<b>CATALOG NUMBER</b>	FWP-50A14F
<b>UPC</b>	051712370868
<b>PRODUCT LENGTH/DEPTH</b>	51 mm
<b>PRODUCT HEIGHT</b>	15 mm
<b>PRODUCT WIDTH</b>	15 mm
<b>PRODUCT WEIGHT</b>	21.2 g
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	UL Recognized CSA Certified

## 0000

USED WITH	Finger safe holders/blocks and striker
AMPERAGE RATING	50 A
ACCESSORIES	<ul style="list-style-type: none"> <li>CH14 Modular fuse holder</li> <li>FW14-PCB</li> </ul>
BREAKING CAPACITY	200 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
FUSE INDICATOR	Non Indicating
RELEASE CHARACTERISTIC	Other
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
FUSE SIZE	14 x 51 mm
RATED VOLTAGE AC	700 V
RATED VOLTAGE DC	800 V
CLASS	Class aR
CLEARING (I2T)	1800
WATT LOSSES	9 W
FUSE SHAPE	Cylindrical
MINIMUM MELTING	200 I2t (A2 sec)
PRE ARC (I2T)	200
COLOR	White
INTERRUPT RATING	200 kAIC
CONNECTION	Ferrule end x ferrule end
CONSTRUCTION SIZE	14 mm x 51 mm
MATERIAL	Ceramic
PACKAGING TYPE	Standard
QUANTITY	10
VOLTAGE RATING	700 V
TYPE	High speed fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
FUSE TYPE	FWP-A14F
BREAKING CAPACITY AT NOMINAL VOLTAGE, AC	200 kA
BREAKING CAPACITY AT	50 kA

## 00

DECLARATIONS OF CONFORMITY	<a href="#">eaton-high-speed-cylindrical-fuse-declaration-of-conformity-uk250904en.pdf</a>
00000	<a href="#">720025 FWP</a>

NOMINAL VOLTAGE, DC

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

