



□□□□□

## Eaton FWP-5B

Eaton Bussmann series FWP high speed fuse, 250 Vac/dc, 5A, 200 kAIC Vac, 50 kAIC at 700 Vdc, None, High speed fuse, Blade end X blade end, Stud

□□□□

PRODUCT NAME	Eaton Bussmann series high speed cylindrical fuse
CATALOG NUMBER	FWP-5B
UPC	051712557849
PRODUCT LENGTH/DEPTH	60 mm
PRODUCT HEIGHT	40 mm
PRODUCT WIDTH	86 mm
PRODUCT WEIGHT	25.4 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized CSA Certified



Powering Business Worldwide

AMPERAGE RATING	5 A
BREAKING CAPACITY	50 kA
FUSE INDICATOR	Non Indicating
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
RATED SWITCHING CAPACITY	50 A
RATED VOLTAGE AC	700 V
RATED VOLTAGE DC	700 V
MOUNTING DIMENSION	M6
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	63.35 mm
CURRENT TYPE	AC/DC
CLASS	Class aR
CLEARING (I2T)	10 at 700 V
WATT LOSSES	1.5 W
FUSE SHAPE	Cylindrical, center bolted tags
PRE ARC (I2T)	1.6
COLOR	None
INTERRUPT RATING	50 kAIC at 700 Vdc 200 kAIC Vac
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Stud
PACKAGING TYPE	Standard
VOLTAGE RATING	700 Vac, 700 Vdc (UL)
TYPE	High speed fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
FUSE TYPE	FWP-B
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

