

Eaton FWP-63A14F

Eaton Bussmann series FWP high speed fuse, 700 Vdc (UL), 63A, 50 kAIC at 700 Vdc, Non Indicating, High speed fuse, Ferrule end X ferrule end, Class aR, White, Ceramic

PRODUCT NAME	Eaton Bussmann series high speed cylindrical fuse
CATALOG NUMBER	FWP-63A14F
PRODUCT LENGTH/DEPTH	51 mm
PRODUCT HEIGHT	15 mm
PRODUCT WIDTH	15 mm
PRODUCT WEIGHT	21.2 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL

AMPERAGE RATING	63 A
ACCESSORIES	<ul style="list-style-type: none"> • CH14 Modular fuse holder • FW14-PCB
BREAKING CAPACITY	50 kA
FUSE INDICATOR	Non Indicating
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	DC
FUSE SIZE	14 x 51 mm
CLASS	Class aR
WATT LOSSES	10 W
FUSE SHAPE	Cylindrical
COLOR	White
INTERRUPT RATING	50 kAIC
CONNECTION	Ferrule end x ferrule end
CONSTRUCTION SIZE	14 mm x 51 mm
MATERIAL	Ceramic
VOLTAGE RATING	700 V
TYPE	High speed fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
FUSE TYPE	FWP-A14F

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

: