

Eaton HDD601-0000

Eaton HDD Duplex High Pressure Filter,
HDD601.80G.30.E.P.-.FS.8.P.-.S1.VS5.2,5.P.-
.NO., 80 G, Stainless steel wire mesh (G),
Nitrile, 4538 psi (315 Bar), Bypass set at 51
psi (3.5 Bar)

PRODUCT NAME	Eaton HDD Duplex High Pressure Filter
CATALOG NUMBER	HDD601-0000
PRODUCT LENGTH/DEPTH	330 mm
PRODUCT HEIGHT	557 mm
PRODUCT WIDTH	388 mm
PRODUCT WEIGHT	145 kg
COMPLIANCES	PED 2014/68/EU for mineral oil (fluid group 2), Article 4, Para. 3. ATEX Directive 2014/34/EU AD 2000

CONNECTION TYPE	2" SAE/ANSI flange
FILTER TYPE	High pressure filter Duplex filter
MATERIAL	Carbon steel EN-GJS-400-18-LT
RETENTION RATING	5.0 µ m
APPLICATION	For continuous operation. Mount in suction, pressure or return lines
SPECIFICATION	Standard
CODE STAMP	None
FILTER FINENESS	80 G
FILTER MEDIA TYPE	Stainless steel wire mesh (G)
FLUID GROUP (DGRL 2014/68/EU)	2
INDICATOR TYPE	Electrical/Visual
SEALING MATERIAL	Nitrile
ELEMENT COLLAPSE RATING	435 psi (30 Bar)
OPERATING TEMPERATURE - MAX	100 °C
OPERATING TEMPERATURE - MIN	-10 °C
VALVE CONFIGURATION OPTIONS	Bypass set at 51 psi (3.5 Bar)
OPERATING PRESSURE - MAX	4538 psi (315 Bar)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

