

Eaton HRC1

Eaton Crouse-Hinds series HRC bimetal thermostat, 0.5 HP/1 HP, Copper-free aluminum, 1-pole, 2.5°F (1.5°C) temp. diff, 36° to 82°F (2° to 28°C) temp. range, Single-throw, 3/4", For heating applications only, 120/250 Vac

PRODUCT NAME	Eaton Crouse-Hinds series HRC bimetal thermostat
CATALOG NUMBER	HRC1
UPC	782274177373
PRODUCT LENGTH/DEPTH	5.92 in
PRODUCT HEIGHT	5.92 in
PRODUCT WIDTH	4.38 in
PRODUCT WEIGHT	2.35 lb

SPECIAL FEATURES	Bimetal sensing element
TYPE	For heating applications only
VOLTAGE RATING	120/250 Vac
AMPERAGE RATING	22 A
AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 1 Class I, Division 2 Class II, Division 1 Class II, Division 2 Class III
HORSEPOWER	0.5 hp at 120 Vac, 1 hp at 250 Vac
NUMBER OF POLES	Single-pole
TEMPERATURE DIFFERENTIAL	2.5°F (1.5°C)
TEMPERATURE RANGE	36°-82°F (2°-28°C)
THROW	Single-throw
TRADE SIZE	3/4"
MATERIAL	Copper-free aluminum

IF 1234 - HRC Series Explosionproof Thermostats	
Eaton Specification Sheet - HRC1	
HRC Series Explosionproof Thermostats catalog page	
HRC Explosionproof Thermostats UL certification	

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

