

## Eaton FWX-20A14F

Eaton Bussmann series FWX high speed fuse, 600V, 20A, 200 kAIC Vac, 50 kAIC at 250 Vdc, Non Indicating, High speed fuse, Ferrule end X ferrule end

PRODUCT NAME	Eaton Bussmann series high speed cylindrical fuse
CATALOG NUMBER	FWX-20A14F
UPC	051712795586
PRODUCT LENGTH/DEPTH	55 mm
PRODUCT HEIGHT	32 mm
PRODUCT WIDTH	73 mm
PRODUCT WEIGHT	20.3 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized

AMPERAGE RATING	2000 A
ACCESSORIES	<ul style="list-style-type: none"> <li>• CH14 Modular fuse holder</li> <li>• FW14-PCB</li> </ul>
BREAKING CAPACITY	200 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
FUSE INDICATOR	Other
RELEASE CHARACTERISTIC	Other
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	14 x 51 mm
RATED VOLTAGE AC	250 V
RATED VOLTAGE DC	250 V
CLASS	Class aR
CLEARING (I2T)	200 at 250 V
WATT LOSSES	4.6 W
FUSE SHAPE	Cylindrical
PRE ARC (I2T)	33
INTERRUPT RATING	200 kAIC
CONNECTION	Ferrule end x ferrule end
CONSTRUCTION SIZE	14 mm x 51 mm
MATERIAL	Ceramic
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V
TYPE	High speed fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
FUSE TYPE	FWX-A14F
BREAKING CAPACITY AT NOMINAL VOLTAGE, AC	200 kA
BREAKING CAPACITY AT NOMINAL VOLTAGE, DC	50 kA



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com  
© 2025

Follow us on social media to get the latest product and support information.

