

## Eaton FWX-5A14F

Eaton Bussmann series FWX high speed fuse, 600V, 5A, 200 kAIC Vac, 50 kAIC at 250 Vdc, Non Indicating, High speed fuse, Ferrule end X ferrule end

<b>PRODUCT NAME</b>	Eaton Bussmann series high speed cylindrical fuse
<b>CATALOG NUMBER</b>	FWX-5A14F
<b>UPC</b>	051712795548
<b>PRODUCT LENGTH/DEPTH</b>	55 mm
<b>PRODUCT HEIGHT</b>	32 mm
<b>PRODUCT WIDTH</b>	73 mm
<b>PRODUCT WEIGHT</b>	21.2 g
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	UL Recognized



AMPERAGE RATING	50 A
ACCESSORIES	<ul style="list-style-type: none"><li>• CH14 Modular fuse holder</li><li>• FW14-PCB</li></ul>
BREAKING CAPACITY	200 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
FUSE INDICATOR	Non Indicating
RELEASE CHARACTERISTIC	Other
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
FUSE SIZE	14 x 51 mm
RATED VOLTAGE AC	250 V
RATED VOLTAGE DC	250 V
CLASS	Class aR
CLEARING (I2T)	13 at 250 V
WATT LOSSES	1.3 W
FUSE SHAPE	Cylindrical
PRE ARC (I2T)	1.6
INTERRUPT RATING	200 kAIC
CONNECTION	Ferrule end x ferrule end
CONSTRUCTION SIZE	14 mm x 51 mm
MATERIAL	Ceramic
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V
TYPE	High speed fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
FUSE TYPE	FWX-A14F
BREAKING CAPACITY AT NOMINAL VOLTAGE, AC	200 kA
BREAKING CAPACITY AT NOMINAL VOLTAGE, DC	50 kA



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

