

Eaton HRC2

Eaton Crouse-Hinds series HRC bimetal thermostat, 0.5 HP/1 HP, Copper-free alum, 1-pole, 2.5°F (1.5°C) temp. diff, 36° to 82°F (2° to 28°C) temp. range, Double-throw, 3/4", For heating or cooling/ventilation, 120/250 Vac

PRODUCT NAME	Eaton Crouse-Hinds series HRC bimetal thermostat
CATALOG NUMBER	HRC2
UPC	782274154619
PRODUCT LENGTH/DEPTH	4.92 in
PRODUCT HEIGHT	4.92 in
PRODUCT WIDTH	3.38 in
PRODUCT WEIGHT	3 lb

SPECIAL FEATURES	Bimetal sensing element
TYPE	For heating or cooling/ventilation applications
VOLTAGE RATING	120/250 Vac
AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 1 Class I, Division 2 Class II, Division 1 Class II, Division 2 Class III
HORSEPOWER	0.5 hp at 120 Vac, 1 hp at 250 Vac
NUMBER OF POLES	Single-pole
TEMPERATURE DIFFERENTIAL	2.5°F (1.5°C)
TEMPERATURE RANGE	36°-82°F (2°-28°C)
THROW	Double-throw
TRADE SIZE	3/4"
MATERIAL	Copper-free aluminum

	IF 1234 - HRC Series Explosionproof Thermostats
	Eaton Specification Sheet - HRC2
	HRC Series Explosionproof Thermostats catalog page
	HRC Explosionproof Thermostats UL certification

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

: