



□□□□

## Eaton LUM22211

Eaton CrystalWay 24-48/45 XL

□□□□

<b>PRODUCT NAME</b>	Eaton CrystalWay CPS Emergency luminaire
<b>CATALOG NUMBER</b>	LUM22211
<b>PRODUCT LENGTH/DEPTH</b>	330 mm
<b>PRODUCT HEIGHT</b>	183 mm
<b>PRODUCT WIDTH</b>	28 mm
<b>PRODUCT WEIGHT</b>	0.95 kg
<b>CERTIFICATIONS</b>	CE



Powering Business Worldwide



<b>BATTERY QUALITY</b>	Other
<b>PROTECTION CLASS</b>	II
<b>OUTDOOR USE COMPLIANCE</b>	True
<b>DEGREE OF PROTECTION</b>	IP42
<b>LAMP TYPE</b>	LED not exchangeable
<b>WITH LIGHT SOURCE</b>	True
<b>LAMP HOLDER</b>	Other
<b>TYPE OF INDICATOR</b>	Single/double-sided
<b>MONITORING EQUIPMENT</b>	None
<b>POWER SUPPLY SYSTEM</b>	Central (central battery)
<b>VOLTAGE TYPE</b>	DC
<b>WITH REMOTE SWITCH CONNECTION</b>	False
<b>CONDUCTOR CROSS SECTION</b>	2.5
<b>CONNECTION TYPE</b>	Plug-in connection
<b>MAX. SYSTEM POWER</b>	1.9 W
<b>RATED LIFE TIME L70/B50 AT 25 °C</b>	50000 s
<b>TYPE OF CONTROL GEAR</b>	LED operating device current-controlled
<b>TYPE OF WIRING</b>	Through wiring included
<b>NOMINAL VOLTAGE AC - MAX</b>	48 V
<b>NOMINAL VOLTAGE AC - MIN</b>	24 V
<b>MATERIAL HOUSING</b>	Plastic
<b>COLOR HOUSING</b>	White
<b>MATERIAL COVER</b>	Plastic, transparent
<b>LABELLING TYPE</b>	Insert sheet/plate
<b>PICTOGRAM INCLUDED</b>	True
<b>NUMBER OF POLES (NUMERIC)</b>	3
<b>IMPACT STRENGTH</b>	IK04
<b>RATED LUMINOUS FLUX ACC. IEC 62722-2-1</b>	45 J
<b>LIGHT DISTRIBUTOR</b>	Diffuser lens/optic/panel
<b>FUNCTION</b>	Escape route signage
<b>LUMINAIRE WITH LIMITED SURFACE TEMPERATURE, SIGN D</b>	False
<b>NUMBER OF LIGHTING HEADS</b>	36



