



□□□□□

Eaton GSGB225

Fuse-link, high speed, 225 A, AC 660 V, DC 350 V, BS88, 35 x 107 mm, aR, BS, Ultra fast

□□□□

PRODUCT NAME	Eaton Bussmann series high speed british standard fuse
CATALOG NUMBER	GSGB225
PRODUCT LENGTH/DEPTH	54 mm
PRODUCT HEIGHT	14 mm
PRODUCT WIDTH	78 mm
PRODUCT WEIGHT	202 g
COMPLIANCES	CE

□□□□

□□

AMPERAGE RATING	225 A
BREAKING CAPACITY	100 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
RATED SWITCHING CAPACITY	100 kA
RATED VOLTAGE AC	660 V
RATED VOLTAGE DC	350 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	81.7 mm
MOUNTING DIMENSION	M10
CURRENT TYPE	AC/DC
CLASS	Class aR
WATT LOSSES	45 W
FUSE SHAPE	Offset bolted tags
COLOR	None
CONSTRUCTION SIZE	Other
VOLTAGE RATING	660 V
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	GSG
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

