



□□□□□

Eaton GSGB630

Fuse-link, high speed, 630 A, AC 660 V, DC 350 V, BS88, 81 x 143 mm, aR, BS, Ultra fast

□□□□

PRODUCT NAME	Eaton Bussmann series high speed british standard fuse
CATALOG NUMBER	GSGB630
PRODUCT LENGTH/DEPTH	143 mm
PRODUCT HEIGHT	80.8 mm
PRODUCT WIDTH	73.8 mm
PRODUCT WEIGHT	0.015 g
COMPLIANCES	CE

□□□□

AMPERAGE RATING	630 A
BREAKING CAPACITY	100 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
RATED SWITCHING CAPACITY	100 kA
RATED VOLTAGE AC	660 V
RATED VOLTAGE DC	350 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	110 mm
MOUNTING DIMENSION	M10
CURRENT TYPE	AC/DC
CLASS	Class aR
WATT LOSSES	117 W
FUSE SHAPE	Offset 4 barrel bolted tags
COLOR	None
CONSTRUCTION SIZE	Other
VOLTAGE RATING	660 V
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	GSG
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

□□

