



Eaton N002-010-BL

Cat5e 350 MHz Molded (UTP) Ethernet Cable
(RJ45 M/M) - Blue, 10 ft. (3.05 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated copper patch cables
CATALOG NUMBER	N002-010-BL
UPC	037332012814
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.22 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS REACH
CERTIFICATIONS	cUL Listed UL Listed

SPECIAL FEATURES	0% to 90% RH, Non-Condensing
CABLE JACKET RATING	CM
CABLE JACKET COLOR	Blue
PACKAGE CONTENTS	10-ft. (3.05 m) Cat5e Blue Patch Cable Molded 350MHz
SYSTEM REQUIREMENTS	Cat5/5e For 1000Base-T (1Gbps Ethernet), 10/100Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type3 applications.
IEEE STANDARDS SUPPORTED	802.3ab 802.3at
CONNECTOR TYPE	Networking-copper
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	1 Gbps (Gigabit)
PRODUCT HIGHLIGHTS	IEEE 802.3ab Lifetime limited warranty (Worldwide) PVC 4-pair stranded UTP All cables feature boots with integral strain-relief and RJ45 (Male) connectors Premium cabling for Category 5 and 5e applications—rated for 350 MHz/1 Gbps communications
CONTACT PLATING	Gold
SIDE A CONNECTOR1	RJ45 (MALE)
SIDE B CONNECTOR1	RJ45 (MALE)
SIDE B CONNECTOR3	RJ45 (MALE)
TECHNOLOGY	Cat5/5e
OPERATING HUMIDITY	0% to 90% RH, Non-Condensing
OPERATING TEMPERATURE RANGE	14° to 104°F (-10° to 40°C)
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE TEMPERATURE	5° to 122°F (-15° to 50°C)
CONDUCTOR GAUGE	26 AWG
CABLE LENGTH	10 Foot
OUTER CABLE DIAMETER	5.0 mm
NUMBER OF CONDUCTORS	4 Pair

OPERATING TEMPERATURE	14° to 104°F (-10° to 40°C)
BANDWIDTH PER TIA STANDARD	100 MHz
MAXIMUM BANDWIDTH AS TESTED	350 MHz
CABLE SHIELDING	UTP
CABLE LENGTH RANGE	9 - 14ft (2 - 4M)
CABLE SHEATH MATERIAL	UTP
CONNECTOR GROUP	RJ45
CONDUCTOR MATERIAL	Stranded Copper
CONNECTOR	RJ45 (male)
POE TYPE	Type 2 PoE+ (30W, IEEE 802.3at)
WIRING METHOD	EIA/TIA 568B
CABLE TYPE	Regular
CABLE STYLE	Molded
