



Eaton N125-025-GY

Cat6 Gigabit Molded Shielded (FTP) Ethernet Cable (RJ45 M/M), Gray, 25 ft. (7.62 m)



| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Tripp Lite series preterminated copper patch cables |
| CATALOG NUMBER | N125-025-GY |
| UPC | 037332135438 |
| PRODUCT LENGTH/DEPTH | 0.5 in |
| PRODUCT HEIGHT | 10 in |
| PRODUCT WIDTH | 8 in |
| PRODUCT WEIGHT | 0.8 lb |
| COMPLIANCES | IEEE Certified REACH RoHS |
| CERTIFICATIONS | UL Listed cUL Listed |



Powering Business Worldwide



| | |
|------------------------------------|--|
| SPECIAL FEATURES | 0% to 90% RH, Non-Condensing |
| CABLE JACKET RATING | CMG |
| CABLE JACKET COLOR | Gray |
| PACKAGE CONTENTS | 25-ft. (7.62 m) Gray Cat6 Shielded FTP Patch Cable |
| SYSTEM REQUIREMENTS | Cat6 |
| IEEE STANDARDS SUPPORTED | 802.3at 802.3an |
| CONNECTOR TYPE | Networking-copper |
| PRODUCT FEATURES | PoE Support |
| CABLE JACKET MATERIAL | PVC |
| NETWORK SPEED | 1 Gbps (Gigabit) |
| PRODUCT HIGHLIGHTS | Molded boot provides extra strain-relief and durability Protect your network data from EMI/RFI interference |
| CONTACT PLATING | Gold |
| SIDEA CONNECTOR1 | RJ45 (MALE) |
| SIDEB CONNECTOR1 | RJ45 (MALE) |
| SIDEB CONNECTOR3 | RJ45 (MALE) |
| TECHNOLOGY | Cat6 |
| OPERATING HUMIDITY | 0% to 90% RH, Non-Condensing |
| OPERATING TEMPERATURE RANGE | 14° to 104°F (-10° to 40°C) |
| STORAGE HUMIDITY RANGE | 0% to 90% RH, Non-Condensing |
| STORAGE TEMPERATURE | 5° to 122°F (-15° to 50°C) |
| CONDUCTOR GAUGE | 26 AWG |
| CABLE LENGTH | 25 Foot |
| OUTER CABLE DIAMETER | 5.8 mm |
| NUMBER OF CONDUCTORS | 4 Pair |
| OPERATING TEMPERATURE | 14° to 104°F (-10° to 40°C) |
| BANDWIDTH PER TIA STANDARD | 250 MHz |
| MAXIMUM BANDWIDTH AS TESTED | 500 MHz |
| CABLE SHIELDING | F/UTP |
| CABLE LENGTH RANGE | 20 - 50ft (6 - 15M) |
| CABLE SHEATH MATERIAL | FTP |



