



Eaton N200-100-WH

Cat6 Gigabit Molded (UTP) Ethernet Cable (RJ45 M/M), White. 100 ft. (30.5 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated copper patch cables
CATALOG NUMBER	N200-100-WH
UPC	037332204837
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	17 in
PRODUCT WIDTH	14 in
PRODUCT WEIGHT	2.63 lb
WARRANTY	Limited lifetime
COMPLIANCES	REACH RoHS IEEE Certified
CERTIFICATIONS	UL Listed cUL Listed



Powering Business Worldwide

□□□□	
SPECIAL FEATURES	0% to 90% RH, Non-Condensing
CABLE JACKET RATING	CM
CABLE JACKET COLOR	White
PACKAGE CONTENTS	N200-100-WH Cat6 Gigabit Molded Patch Cable, White, 100-ft. (30.5 m)
SYSTEM REQUIREMENTS	Cat6 PoE
IEEE STANDARDS SUPPORTED	802.3at 802.3an
CONNECTOR TYPE	Networking-copper
PRODUCT FEATURES	PoE Support
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	1 Gbps (Gigabit)
PRODUCT HIGHLIGHTS	Rated for 550 MHz/1 Gbps communication 24 AWG 4-pair solid UTP with PVC jacket Lifetime limited warranty (Worldwide) Gold-plated copper contacts minimize data loss Integral strain relief protects connectors from stress and cracking Premium cabling for Cat5/5e/6 home/office network applications
CONTACT PLATING	Gold
SIDEA CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR3	RJ45 (MALE)
TECHNOLOGY	Cat6
OPERATING HUMIDITY	0% to 90% RH, Non-Condensing
OPERATING TEMPERATURE RANGE	14° to 104°F (-10° to 40°C)
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE TEMPERATURE	5° to 122°F (-15° to 50°C)
CONDUCTOR GAUGE	24 AWG
CABLE LENGTH	100 Foot
OUTER CABLE DIAMETER	6.0 mm
WIRE SIZE (AWG) - MAX	24
NUMBER OF CONDUCTORS	4 Pair

□□

OPERATING TEMPERATURE	14° to 104°F (-10° to 40°C)
BANDWIDTH PER TIA STANDARD	250 MHz
MAXIMUM BANDWIDTH AS TESTED	500 MHz
CABLE SHIELDING	UTP
CABLE LENGTH RANGE	50ft and up (15M and up)
CABLE SHEATH MATERIAL	UTP
CONNECTOR GROUP	RJ45
CONDUCTOR MATERIAL	Solid Copper
CONNECTOR	RJ45 (male)
POE TYPE	Type 2 PoE+ (30W, IEEE 802.3at)
POWER OVER ETHERNET (POE)	30W (802.3at)
WIRING METHOD	EIA/TIA 568B
CABLE TYPE	Regular
CABLE STYLE	Molded
