



## Eaton N125-050-GY

Cat6 Gigabit Molded Shielded (FTP) Ethernet Cable (RJ45 M/M), Gray, 50 ft. (15.24 m)



<b>PRODUCT NAME</b>	Eaton Tripp Lite series preterminated copper patch cables
<b>CATALOG NUMBER</b>	N125-050-GY
<b>UPC</b>	037332135445
<b>PRODUCT LENGTH/DEPTH</b>	0.5 in
<b>PRODUCT HEIGHT</b>	10 in
<b>PRODUCT WIDTH</b>	12 in
<b>PRODUCT WEIGHT</b>	1.3 lb
<b>COMPLIANCES</b>	RoHS IEEE Certified REACH
<b>CERTIFICATIONS</b>	UL Listed cUL Listed



Powering Business Worldwide



<b>SPECIAL FEATURES</b>	0% to 90% RH, Non-Condensing
<b>CABLE JACKET RATING</b>	CMG
<b>CABLE JACKET COLOR</b>	Gray
<b>PACKAGE CONTENTS</b>	50-ft. (15.24 m) Gray Cat6 Shielded FTP Patch Cable
<b>SYSTEM REQUIREMENTS</b>	Cat6
<b>IEEE STANDARDS SUPPORTED</b>	802.3an 802.3at
<b>CONNECTOR TYPE</b>	Networking-copper
<b>PRODUCT FEATURES</b>	PoE Support
<b>CABLE JACKET MATERIAL</b>	PVC
<b>NETWORK SPEED</b>	1 Gbps (Gigabit)
<b>PRODUCT HIGHLIGHTS</b>	Protect your network data from EMI/RFI interference Molded boot provides extra strain-relief and durability
<b>CONTACT PLATING</b>	Gold
<b>SIDEA CONNECTOR1</b>	RJ45 (MALE)
<b>SIDEB CONNECTOR1</b>	RJ45 (MALE)
<b>SIDEB CONNECTOR3</b>	RJ45 (MALE)
<b>TECHNOLOGY</b>	Cat6
<b>OPERATING HUMIDITY</b>	0% to 90% RH, Non-Condensing
<b>OPERATING TEMPERATURE RANGE</b>	14° to 104°F (-10° to 40°C)
<b>STORAGE HUMIDITY RANGE</b>	0% to 90% RH, Non-Condensing
<b>STORAGE TEMPERATURE</b>	5° to 122°F (-15° to 50°C)
<b>CONDUCTOR GAUGE</b>	26 AWG
<b>CABLE LENGTH</b>	50 Foot
<b>OUTER CABLE DIAMETER</b>	5.8 mm
<b>NUMBER OF CONDUCTORS</b>	4 Pair
<b>OPERATING TEMPERATURE</b>	14° to 104°F (-10° to 40°C)
<b>BANDWIDTH PER TIA STANDARD</b>	250 MHz
<b>MAXIMUM BANDWIDTH AS TESTED</b>	500 MHz
<b>CABLE SHIELDING</b>	F/UTP
<b>CABLE LENGTH RANGE</b>	20 - 50ft (6 - 15M)
<b>CABLE SHEATH MATERIAL</b>	FTP



