



Eaton N200-015-WH

Cat6 Gigabit Molded (UTP) Ethernet Cable
(RJ45 M/M), White, 15 ft. (4.57 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated copper patch cables
CATALOG NUMBER	N200-015-WH
UPC	037332201959
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	10 in
PRODUCT WIDTH	8 in
PRODUCT WEIGHT	0.41 lb
WARRANTY	Limited lifetime
COMPLIANCES	REACH RoHS IEEE Certified
CERTIFICATIONS	UL Listed cUL Listed

□□□□	
SPECIAL FEATURES	0% to 90% RH, Non-Condensing
CABLE JACKET RATING	CM
CABLE JACKET COLOR	White
PACKAGE CONTENTS	N200-015-WH Cat6 Gigabit Molded Patch Cable, White, 15-ft. (4.57 m)
SYSTEM REQUIREMENTS	Cat6 PoE
IEEE STANDARDS SUPPORTED	802.3at 802.3an
CONNECTOR TYPE	Networking-copper
PRODUCT FEATURES	PoE Support
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	1 Gbps (Gigabit)
PRODUCT HIGHLIGHTS	Premium cabling for Cat5/5e/6 home/office network applications Rated for 550 MHz/1 Gbps communication Integral strain relief protects connectors from stress and cracking 24 AWG 4-pair solid UTP with PVC jacket Lifetime limited warranty (Worldwide) Gold-plated copper contacts minimize data loss
CONTACT PLATING	Gold
SIDEA CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR3	RJ45 (MALE)
TECHNOLOGY	Cat6
OPERATING HUMIDITY	0% to 90% RH, Non-Condensing
OPERATING TEMPERATURE RANGE	14° to 104°F (-10° to 40°C)
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE TEMPERATURE	5° to 122°F (-15° to 50°C)
CONDUCTOR GAUGE	24 AWG
CABLE LENGTH	15 Foot
OUTER CABLE DIAMETER	6.0 mm
NUMBER OF CONDUCTORS	4 Pair
OPERATING	14° to 104°F (-10° to 40°C)

□□	
----	--

TEMPERATURE	
BANDWIDTH PER TIA STANDARD	250 MHz
MAXIMUM BANDWIDTH AS TESTED	500 MHz
CABLE SHIELDING	UTP
CABLE LENGTH RANGE	14 - 20ft (4 - 6M)
CABLE SHEATH MATERIAL	UTP
CONNECTOR GROUP	RJ45
CONDUCTOR MATERIAL	Solid Copper
CONNECTOR	RJ45 (male)
POE TYPE	Type 2 PoE+ (30W, IEEE 802.3at)
POWER OVER ETHERNET (POE)	30W (802.3at)
WIRING METHOD	EIA/TIA 568B
CABLE TYPE	Regular
CABLE STYLE	Molded
