



Eaton N201-025-GY

Cat6 Gigabit Snagless Molded (UTP) Ethernet Cable (RJ45 M/M), Gray, 25 ft. (7.62 m)



PRODUCT NAME	Eaton Tripp Lite series preterminated copper patch cables
CATALOG NUMBER	N201-025-GY
UPC	037332100009
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	10 in
PRODUCT WIDTH	8 in
PRODUCT WEIGHT	0.69 lb
COMPLIANCES	RoHS REACH IEEE Certified
CERTIFICATIONS	UL Listed cUL Listed



Powering Business Worldwide

SPECIAL FEATURES	0% to 90% RH, Non-Condensing
CABLE JACKET RATING	CM
CABLE JACKET COLOR	Gray
PACKAGE CONTENTS	25-ft. Cat6 Gray Gigabit Patch Cord Snagless Molded
SYSTEM REQUIREMENTS	Cat6 PoE For 1000 Base-T (1Gbps Ethernet), 10/100 Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring TYPE 3 applications as well as EIA/TIA applications.
IEEE STANDARDS SUPPORTED	802.3an 802.3at
CONNECTOR TYPE	Networking-copper
PRODUCT FEATURES	Snagless Connector PoE Support
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	1 Gbps (Gigabit)
PRODUCT HIGHLIGHTS	Premium cabling for Category 6, Category 5e and Category 5 applications—rated for 550 MHz/1Gbps communications All cables feature boots with integral strain-relief and RJ45 (Male) connectors PVC 4-pair solid UTP Designed to meet Category 6 specifications; reduces cross-talk and return loss IEEE 802.3ab
CONTACT PLATING	Gold
SIDEA CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR3	RJ45 (MALE)
TECHNOLOGY	Cat6
OPERATING HUMIDITY	0% to 90% RH, Non-Condensing
OPERATING TEMPERATURE RANGE	14° to 122°F (-10° to 50°C)
STORAGE HUMIDITY	0% to 90% RH, Non-

