



Eaton N201-S10-BL

Cat6 Gigabit Snagless Slim UTP Ethernet Cable (RJ45 M/M), Blue, 10 ft. (3.05 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated copper patch cables
CATALOG NUMBER	N201-S10-BL
UPC	037332230898
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.12 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS REACH
CERTIFICATIONS	UL Listed cUL Listed

□□□□		□□	
SPECIAL FEATURES	5% to 85% RH, Non-Condensing		
CABLE JACKET RATING	CM		
CABLE JACKET COLOR	Blue		
PACKAGE CONTENTS	N201-S10-BL Cat6 UTP Patch Cable RJ45 (M/M), 10-ft. (3.05 m), Blue		
SYSTEM REQUIREMENTS	Cat6 PoE		
IEEE STANDARDS SUPPORTED	802.3af 802.3ab 802.3at		
CONNECTOR TYPE	Networking-copper		
PRODUCT FEATURES	Snagless Connector PoE Support		
CABLE JACKET MATERIAL	PVC		
NETWORK SPEED	1 Gbps (Gigabit)		
PRODUCT HIGHLIGHTS	Color-coded blue for fast, easy identification in a crowded rack or workstation Easy to route around corners and through crowded cable management panels Over 38% slimmer than standard Cat6 cables to increase airflow in full racks Snagless RJ45 connectors prevent tabs from being damaged during installation Cat6 UTP patch cord rated for high-speed 1 Gbps communications Lifetime limited warranty (Worldwide)		
CONTACT PLATING	Gold		
SIDEA CONNECTOR1	RJ45 (MALE)		
SIDEB CONNECTOR1	RJ45 (MALE)		
SIDEB CONNECTOR3	RJ45 (MALE)		
TECHNOLOGY	Cat6		
OPERATING HUMIDITY	5% to 85% RH, Non-Condensing		
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)		
STORAGE HUMIDITY RANGE	5% to 85% RH, Non-Condensing		
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)		

CONDUCTOR GAUGE	28 AWG
CABLE LENGTH	10 Foot
OUTER CABLE DIAMETER	3.8 mm
WIRE SIZE (AWG) - MAX	3.8
NUMBER OF CONDUCTORS	4 Pair
OPERATING TEMPERATURE	-4° to 140°F (-20° to 60°C)
BANDWIDTH PER TIA STANDARD	250 MHz
MAXIMUM BANDWIDTH AS TESTED	550 MHz
CABLE SHIELDING	UTP
CABLE LENGTH RANGE	9 - 14ft (2 - 4M)
CABLE SHEATH MATERIAL	UTP
CONNECTOR GROUP	RJ45
CONDUCTOR MATERIAL	Stranded Copper
CONNECTOR	RJ45 (male)

POE TYPE	Type 1 PoE (15.4W, IEEE 802.3af) Type 2 PoE+ (30W, IEEE 802.3at)
POWER OVER ETHERNET (POE)	15.4W (802.3af) 30W (802.3at)
WIRING METHOD	EIA/TIA 568B
CABLE TYPE	Slim
CABLE STYLE	Slim Snagless

□□□□:
□□□□:
□□□:
□□: