



Eaton N222-01K-GY

Cat6 Gigabit Solid Core UTP PVC Bulk
Ethernet Cable, Gray, 1000 ft. (304.8 m), TAA

□□□□

PRODUCT NAME	Eaton Tripp Lite series bulk cable
CATALOG NUMBER	N222-01K-GY
UPC	037332117090
PRODUCT LENGTH/DEPTH	13.78 in
PRODUCT HEIGHT	13.78 in
PRODUCT WIDTH	14.17 in
PRODUCT WEIGHT	28 lb
WARRANTY	Limited lifetime
COMPLIANCES	CE Marked REACH RoHS FCC Compliant

CABLE JACKET RATING	CMR
CABLE JACKET COLOR	Gray
PACKAGE CONTENTS	1000-ft. Cat6 Gigabit Bulk Solid Gray PVC Cable
SYSTEM REQUIREMENTS	Cat6 For 1000 Base-T (1Gbps Ethernet), 10/100 Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring TYPE 3 applications as well as EIA/TIA applications
IEEE STANDARDS SUPPORTED	802.3ab
CONNECTOR TYPE	Networking-copper Bare Wire
PRODUCT FEATURES	TAA Compliant
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	1 Gbps (Gigabit)
PRODUCT HIGHLIGHTS	Drastically reduce impedance and structural return loss compared to standard 100Mhz wire 4pr Solid Conductor - CMR PVC Jacket Lifetime limited warranty (Worldwide) Meets category 6 cabling standards
SIDEA CONNECTOR1	BARE WIRE
SIDEB CONNECTOR1	BARE WIRE
SIDEB CONNECTOR3	BARE WIRE
TECHNOLOGY	Cat6
OPERATING TEMPERATURE RANGE	-4° to 167°F (-20° to 75°C)
STORAGE HUMIDITY RANGE	32° to 140°F (0° to 60°C)
STORAGE TEMPERATURE	32° to 140°F (0° to 60°C)
CONDUCTOR GAUGE	23 AWG
CABLE LENGTH	1000 Foot
OUTER CABLE DIAMETER	6.2 mm
NUMBER OF CONDUCTORS	4 Pair
OPERATING TEMPERATURE	-4° to 167°F (-20° to 75°C)
BANDWIDTH PER TIA STANDARD	250 MHz

MAXIMUM BANDWIDTH AS TESTED	500 MHz
CABLE SHIELDING	UTP
CABLE LENGTH RANGE	50ft and up (15M and up)
TAA COMPLIANCE	Yes
CABLE SHEATH MATERIAL	UTP
CONNECTOR GROUP	Bulk cable
CONDUCTOR MATERIAL	Solid Copper
CONNECTOR	Bare wire
CABLE TYPE	Bulk
CABLE STYLE	Solid Bulk
