



Eaton N261-100-BL

Cat6a 10G Snagless Molded UTP Ethernet Cable (RJ45 M/M), PoE, Blue, 100 ft. (30.5 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated copper patch cables
CATALOG NUMBER	N261-100-BL
UPC	037332277596
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	17 in
PRODUCT WIDTH	14 in
PRODUCT WEIGHT	2.52 lb
WARRANTY	Limited lifetime
COMPLIANCES	CE Marked IEEE Certified REACH RoHS UKCA
CERTIFICATIONS	UL Listed cUL Listed

SPECIAL FEATURES	5% to 85% RH, Non-Condensing
CABLE JACKET RATING	CM
CABLE JACKET COLOR	Blue
PACKAGE CONTENTS	N261-100-BL Cat6a 10G Snagless Molded UTP Ethernet Cable (RJ45 M/M), PoE, Blue, 100 ft. (30.5 m)
SYSTEM REQUIREMENTS	PoE Cat6a
CONNECTOR PLATING	Nickel
IEEE STANDARDS SUPPORTED	802.3af 802.3at 802.3ab 802.3an
CONNECTOR TYPE	Networking-copper
PRODUCT FEATURES	Snagless Connector PoE Support
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	10 Gbps
PRODUCT HIGHLIGHTS	Snagless RJ45 connectors prevent tabs from being damaged during installation Blue jacket permits fast, easy identification in a crowded switch or patch panel Lifetime limited warranty (Worldwide) Allows installation of PoE devices in hard-to-reach areas or away from AC outlets Cat6a UTP Ethernet cable rated for high-speed 10 Gbps communications Supports PoE to save you expense and effort of powering PoE devices individually
CONTACT PLATING	Gold
SIDEA CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR3	RJ45 (MALE)
TECHNOLOGY	Cat6a
FEATURES	Flex Center
OPERATING HUMIDITY	5% to 85% RH, Non-Condensing
OPERATING	-4° to 140°F (-20° to 60°C)

TEMPERATURE RANGE	
STORAGE HUMIDITY RANGE	5% to 85% RH, Non-Condensing
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
CONDUCTOR GAUGE	24 AWG
CABLE LENGTH	100 Foot
OUTER CABLE DIAMETER	6.0 mm
NUMBER OF CONDUCTORS	4 Pair
OPERATING TEMPERATURE	-4° to 140°F (-20° to 60°C)
BANDWIDTH PER TIA STANDARD	500 MHz
MAXIMUM BANDWIDTH AS TESTED	500 MHz
CABLE SHIELDING	UTP
CABLE LENGTH RANGE	50ft and up (15M and up)
CABLE SHEATH MATERIAL	UTP
CONNECTOR GROUP	RJ45
CONDUCTOR MATERIAL	Stranded Copper
CONNECTOR	RJ45 (male)
POE TYPE	Type 1 PoE (15.4W, IEEE 802.3af) Type 2 PoE+ (30W, IEEE 802.3at)
POWER OVER ETHERNET (POE)	15.4W (802.3af) 30W (802.3at)
WIRING METHOD	EIA/TIA 568B
CABLE STYLE	Molded Snagless
