



Eaton N201-100-BL

Cat6 Gigabit Snagless Molded (UTP) Ethernet Cable (RJ45 M/M), Blue, 100 ft. (30.5 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated copper patch cables
CATALOG NUMBER	N201-100-BL
UPC	037332173102
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	17 in
PRODUCT WIDTH	14 in
PRODUCT WEIGHT	2.62 lb
COMPLIANCES	RoHS REACH IEEE Certified
CERTIFICATIONS	UL Listed cUL Listed

SPECIAL FEATURES	0% to 90% RH, Non-Condensing
CABLE JACKET RATING	CM
CABLE JACKET COLOR	Blue
PACKAGE CONTENTS	100-ft. (30.5 m) Cat6 Blue Gigabit Patch Cord Snagless Molded
SYSTEM REQUIREMENTS	Cat6 PoE
IEEE STANDARDS SUPPORTED	802.3an 802.3at
CONNECTOR TYPE	Networking-copper
PRODUCT FEATURES	Snagless Connector PoE Support
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	1 Gbps (Gigabit)
PRODUCT HIGHLIGHTS	IEEE 802.3ab PVC 4-pair solid UTP Designed to meet Category 6 specifications; reduces cross-talk and return loss Premium cabling for Category 6, Category 5e and Category 5 applications—rated for 550 MHz/1 Gbps communications All cables feature boots with integral strain-relief and RJ45 (Male) connectors Lifetime limited warranty (Worldwide)
CONTACT PLATING	Gold
SIDEA CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR3	RJ45 (MALE)
TECHNOLOGY	Cat6
OPERATING HUMIDITY	0% to 90% RH, Non-Condensing
OPERATING TEMPERATURE RANGE	14° to 122°F (-10° to 50°C)
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE TEMPERATURE	5° to 140°F (-15° to 60°C)
CONDUCTOR GAUGE	24 AWG
CABLE LENGTH	100 Foot
OUTER CABLE DIAMETER	6.0 mm

NUMBER OF CONDUCTORS	4 Pair
OPERATING TEMPERATURE	14° to 122°F (-10° to 50°C)
BANDWIDTH PER TIA STANDARD	250 MHz
MAXIMUM BANDWIDTH AS TESTED	500 MHz
CABLE SHIELDING	UTP
CABLE LENGTH RANGE	50ft and up (15M and up)
CABLE SHEATH MATERIAL	UTP
CONNECTOR GROUP	RJ45
CONDUCTOR MATERIAL	Solid Copper
CONNECTOR	RJ45 (male)
POE TYPE	Type 2 PoE+ (30W, IEEE 802.3at)
WIRING METHOD	EIA/TIA 568B
CABLE TYPE	Regular
CABLE STYLE	Snagless Molded
