



Eaton N262-014-BL

Cat6a 10G Certified Snagless Shielded STP Ethernet Cable (RJ45 M/M), PoE, Blue, 14 ft. (4.27 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated copper patch cables
CATALOG NUMBER	N262-014-BL
UPC	037332188359
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.43 lb
COMPLIANCES	IEEE Certified REACH RoHS
CERTIFICATIONS	cUL Listed UL Listed

□□□□	
SPECIAL FEATURES	0% to 90% RH, Non-Condensing
CABLE JACKET RATING	CM
CABLE JACKET COLOR	Blue
PACKAGE CONTENTS	14-ft. (4.27 m) Cat6a Blue Patch Cable
SYSTEM REQUIREMENTS	Cat6a
CONNECTOR PLATING	Nickel
IEEE STANDARDS SUPPORTED	802.3at
CONNECTOR TYPE	Networking-copper
PRODUCT FEATURES	Snagless Connector
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	10 Gbps
PRODUCT HIGHLIGHTS	14-ft. (4.27 m) Augmented Cat6 (CAT6a) Shielded (STP) Snagless Patch Cable, Blue 10Gbps Over Copper Each cable Fluke® Tested and Verified Lifetime limited warranty (Worldwide)
CONTACT PLATING	Gold
SIDEA CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR3	RJ45 (MALE)
TECHNOLOGY	Cat6a
OPERATING HUMIDITY	0% to 90% RH, Non-Condensing
OPERATING TEMPERATURE RANGE	14° to 122°F (-10° to 50°C)
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE TEMPERATURE	5° to 140°F (-15° to 60°C)
CONDUCTOR GAUGE	26 AWG
OUTER CABLE DIAMETER	6.2 mm
NUMBER OF CONDUCTORS	4 Pair
OPERATING TEMPERATURE	14° to 122°F (-10° to 50°C)
BANDWIDTH PER TIA STANDARD	500 MHz
MAXIMUM BANDWIDTH AS TESTED	600 MHz
CABLE SHIELDING	STP

□□

CABLE LENGTH RANGE	9 - 14ft (2 - 4M)
CABLE SHEATH MATERIAL	STP
CONNECTOR GROUP	RJ45
CONDUCTOR MATERIAL	Stranded Copper
CONNECTOR	RJ45 (male)
POE TYPE	Type 2 PoE+ (30W, IEEE 802.3at)
POWER OVER ETHERNET (POE)	15.4W (802.3af)
WIRING METHOD	EIA/TIA 568B
CABLE TYPE	Snagless
CABLE STYLE	Snagless
