



Eaton N306-100M

Duplex Multimode 62.5/125 Fiber Patch Cable (SC/SC), 100M (328 ft.)

□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated fiber patch cable
CATALOG NUMBER	N306-100M
UPC	037332157218
PRODUCT LENGTH/DEPTH	4.7 in
PRODUCT HEIGHT	10.2 in
PRODUCT WIDTH	10.2 in
PRODUCT WEIGHT	2.8 lb
COMPLIANCES	RoHS REACH

□□□□	
CABLE JACKET RATING	OFNR
CABLE JACKET COLOR	Orange
PACKAGE CONTENTS	328 -ft. (100 meter) duplex MMF cable SC/SC 62.5/125 fiber
CONNECTOR COLOR	White
SYSTEM REQUIREMENTS	Any fiber optic hardware or NIC card requiring multimode duplex cable with SC/SC connectors
CONNECTOR TYPE	Networking-fiber
CABLE JACKET MATERIAL	LSZH
NETWORK SPEED	10 Gbps 1 Gbps (Gigabit)
PRODUCT HIGHLIGHTS	Attenuation loss meets or exceeds the latest industry standards Premium PVC 62.5/125μ m multimode patch cables
SIDEA CONNECTOR1	SC DUPLEX (MALE)
SIDEB CONNECTOR1	SC DUPLEX (MALE)
TECHNOLOGY	Multimode
OPERATING HUMIDITY	5% to 85% RH, Non-Condensing
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE HUMIDITY RANGE	35% to 65% RH, Non-Condensing
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
BEND RADIUS - MIN	20 mm (Dynamic); 10 mm (Static)
CLAD DIAMETER	125
CORE DIAMETER - MAX	62.5
INSERTION LOSS	≤ 0.20 dB
NUMBER OF FIBERS	2
FIBER CABLE LENGTH	100M (328.1 ft)
CONNECTOR GROUP	SC
CONNECTOR	SC duplex (male)
ATTENUATION 850NM	3.0 dB/km
ENDFACE POLISH	PC
OPTICAL MODE	OM1
FIBER TYPE	62.5/125

□□
