



Eaton N320-10M

Duplex Multimode 62.5/125 Fiber Patch Cable (LC/LC), 10M (33 ft.)

□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated fiber patch cable
CATALOG NUMBER	N320-10M
UPC	037332116901
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.18 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS REACH

CABLE JACKET RATING	OFNR
CABLE JACKET COLOR	Orange
PACKAGE CONTENTS	10 meter Duplex MMF Cable LC/LC 62.5/125 Micron Fiber
CONNECTOR COLOR	Gray
SYSTEM REQUIREMENTS	Any fiber optic hardware or NIC card requiring multimode duplex cable with LC connectors
CONNECTOR TYPE	Networking-fiber
CABLE JACKET MATERIAL	LSZH
NETWORK SPEED	1 Gbps (Gigabit) 10 Gbps
PRODUCT HIGHLIGHTS	Lifetime limited warranty (Worldwide) Manufactured from 62.5/125 duplex (Zipcord) fiber Duplex multimode fiber is most commonly used in LAN applications where links are typically 10 feet or less Fiber Optic Distributed Data Interface (FDDI) Rated Insertion loss testing performed on every connector (0.2dB typical) Length: 10-Meters Connectors: LC connector on each end
SIDEA CONNECTOR1	LC DUPLEX (MALE)
SIDEB CONNECTOR1	LC DUPLEX (MALE)
TECHNOLOGY	Multimode
OPERATING HUMIDITY	5% to 85% RH, Non- Condensing
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE HUMIDITY RANGE	35% to 65% RH, Non- Condensing
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
BEND RADIUS - MIN	20 mm (Dynamic); 10 mm (Static)
CLAD DIAMETER	125
CORE DIAMETER - MAX	62.5
INSERTION LOSS	≤ 0.20 dB
NUMBER OF FIBERS	2

FIBER CABLE LENGTH	10M (32.8 ft)
CONNECTOR GROUP	LC
CONNECTOR	LC duplex (male)
ATTENUATION 850NM	3.0 dB/km
ENDFACE POLISH	PC
OPTICAL MODE	OM1
FIBER TYPE	62.5/125
