



Eaton N261-015-BL

Cat6a 10G Snagless Molded UTP Ethernet Cable (RJ45 M/M), PoE, Blue, 15 ft. (4.6 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated copper patch cables
CATALOG NUMBER	N261-015-BL
UPC	037332277404
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.4 lb
WARRANTY	Limited lifetime
COMPLIANCES	IEEE Certified REACH RoHS
CERTIFICATIONS	UL Listed cUL Listed

SPECIAL FEATURES	5% to 85% RH, Non-Condensing
CABLE JACKET RATING	CM
CABLE JACKET COLOR	Blue
PACKAGE CONTENTS	N261-015-BL Cat6a 10G Snagless Molded UTP Ethernet Cable (RJ45 M/M), PoE, Blue, 15 ft. (4.6 m)
SYSTEM REQUIREMENTS	Cat6a PoE
CONNECTOR PLATING	Nickel
IEEE STANDARDS SUPPORTED	802.3at 802.3an 802.3ab 802.3af
CONNECTOR TYPE	Networking-copper
PRODUCT FEATURES	Snagless Connector PoE Support
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	10 Gbps
PRODUCT HIGHLIGHTS	Snagless RJ45 connectors prevent tabs from being damaged during installation Lifetime limited warranty (Worldwide) Blue jacket permits fast, easy identification in a crowded switch or patch panel Allows installation of PoE devices in hard-to-reach areas or away from AC outlets Supports PoE to save you expense and effort of powering PoE devices individually Cat6a UTP Ethernet cable rated for high-speed 10 Gbps communications
CONTACT PLATING	Gold
SIDE A CONNECTOR1	RJ45 (MALE)
SIDE B CONNECTOR1	RJ45 (MALE)
SIDE B CONNECTOR3	RJ45 (MALE)
TECHNOLOGY	Cat6a
FEATURES	Flex Center
OPERATING HUMIDITY	5% to 85% RH, Non-Condensing
OPERATING	-4° to 140°F (-20° to 60°C)

TEMPERATURE RANGE	
STORAGE HUMIDITY RANGE	5% to 85% RH, Non-Condensing
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
CONDUCTOR GAUGE	24 AWG
CABLE LENGTH	15 Foot
OUTER CABLE DIAMETER	6.0 mm
NUMBER OF CONDUCTORS	4 Pair
OPERATING TEMPERATURE	-4° to 140°F (-20° to 60°C)
BANDWIDTH PER TIA STANDARD	500 MHz
MAXIMUM BANDWIDTH AS TESTED	600 MHz
CABLE SHIELDING	UTP
CABLE LENGTH RANGE	14 - 20ft (4 - 6M)
CABLE SHEATH MATERIAL	UTP
CONNECTOR GROUP	RJ45
CONDUCTOR MATERIAL	Stranded Copper
CONNECTOR	RJ45 (male)
POE TYPE	Type 2 PoE+ (30W, IEEE 802.3at) Type 1 PoE (15.4W, IEEE 802.3af)
POWER OVER ETHERNET (POE)	15.4W (802.3af) 30W (802.3at)
WIRING METHOD	EIA/TIA 568B
CABLE STYLE	Snagless Molded

□□□□:
□□□□:
□□□:
□□: