



Eaton N280-07M-BK

SFP+ 10Gbase-CU Passive Twinax Copper Cable, SFP-H10GB-CU7M Compatible, Black, 7M (22.96 ft.)

□□□□

PRODUCT NAME	Eaton Tripp Lite series direct attach cable
CATALOG NUMBER	N280-07M-BK
UPC	037332178206
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	17 in
PRODUCT WIDTH	14 in
PRODUCT WEIGHT	0.94 lb
COMPLIANCES	RoHS



Powering Business Worldwide

SPECIAL FEATURES	5% to 85% RH
COLOR	Black
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	7 m. (23 ft.) Black 24Awg SFP+ High Speed Passive Copper 10Gbps Cable

SFP+ Direct Attach Cable (DAC) Twinaxial cables conform to SFF-8431 standards, and as such can be used with the following manufacturers equipment that are open to 3rd party cables:
 QLOGIC * EMULEX * JUNIPER * ARISTA * IBM * DELL * EXTREME EMC * BROADCOM * FINISAR * VOLTAIRE * CISCO
 CONFIRMED EQUIPMENT LIST (*ensure the latest firmware and software is installed) CISCO NEXUS * CISCO CATALYST * CISCO CATALYST 3750x CISCO CATALYST 2960 CISCO CATALYST 3500 CISCO CATALYST 3550 CISCO NEXUS 5010 ARISTA 70505-64 QUANTA T3048 EXTREME X250E JUNIPER EX3200 NOT COMPATIBLE TO 3RD PARTY CABLES: HP and BROCADE
 SFP+ Direct Attach Cable (DAC) Twinaxial cables conform to SFF-8431 standards, and as such can be used with the following manufacturers equipment that are open to 3rd party cables:
 QLOGIC * EMULEX * JUNIPER * ARISTA * IBM * DELL * EXTREME EMC * BROADCOM * FINISAR * VOLTAIRE * CISCO
 CONFIRMED EQUIPMENT LIST (*ensure the latest firmware and software is installed) CISCO NEXUS * CISCO CATALYST * CISCO CATALYST 3750x CISCO CATALYST 2960 CISCO CATALYST 3500 CISCO CATALYST 3550 CISCO

SYSTEM REQUIREMENTS

NEXUS 5010 ARISTA
 70505-64 QUANTA T3048
 EXTREME X250E JUNIPER
 EX3200 NOT COMPATIBLE
 TO 3RD PARTY CABLES: HP
 and BROCADE
 SFP+ Direct Attach Cable (DAC)
 Twinaxial cables conform to SFF-8431
 standards, and as such can be used
 with the following manufacturers
 equipment that are open to 3rd
 party cables:
 QLOGIC * EMULEX * JUNIPER *
 ARISTA * IBM * DELL * EXTREME
 EMC * BROADCOM * FINISAR *
 VOLTAIRE * CISCO
 CONFIRMED EQUIPMENT LIST (*ensure
 the latest firmware and software is
 installed)

IEEE STANDARDS SUPPORTED	802.3BA
CONNECTOR TYPE	Networking-copper
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	10 Gbps
PRODUCT HIGHLIGHTS	Fully compliant to MSA SFF-8431 specification Low Cost alternative to Fiber Optic 7 m. (23 ft.) Black 24AWG SFP+ High Speed Passive Copper 10Gbps Cable Equivalent to Cisco SFP-H10GB-CU7M
SIDEA CONNECTOR1	SFP+ (MALE)
SIDEB CONNECTOR1	SFP+ (MALE)
SIDEB CONNECTOR3	SFP+ (MALE)
OPERATING HUMIDITY	5% to 85% RH
OPERATING TEMPERATURE RANGE	32° to 158°F (0° to 70°C)
STORAGE HUMIDITY RANGE	5% to 85% RH
STORAGE TEMPERATURE	-4° to 185°F (-20° to 85°C)
BEND RADIUS - MIN	35mm
AWG-SIZE	24
CABLE LENGTH	23 Foot
OUTER CABLE DIAMETER	6.0mm
OPERATING TEMPERATURE	32° to 158°F (0° to 70°C)

