



Eaton N320-61M

Duplex Multimode 62.5/125 Fiber Patch Cable (LC/LC), 61M (200 ft.)

□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated fiber patch cable
CATALOG NUMBER	N320-61M
UPC	037332155801
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	12 in
PRODUCT WIDTH	10.5 in
PRODUCT WEIGHT	0.001 lb
COMPLIANCES	REACH RoHS

CABLE JACKET RATING	OFNR
CABLE JACKET COLOR	Orange
PACKAGE CONTENTS	200-ft. (60.96 m) Duplex MMF LC/LC 62.5/125 Micron Fiber Cable
CONNECTOR COLOR	Gray
SYSTEM REQUIREMENTS	Any fiber optic hardware or NIC card requiring multimode duplex cable with LC connectors
CONNECTOR TYPE	Networking-fiber
CABLE JACKET MATERIAL	LSZH
NETWORK SPEED	10 Gbps 1 Gbps (Gigabit)
PRODUCT HIGHLIGHTS	Length: 200-ft. (60.96 m) / Connectors: 2 LC connectors on each end Duplex multimode fiber is most commonly used in LAN applications where links are 10 feet or less Manufactured from 62.5/125 duplex (Zipcord) fiber Insertion loss testing performed on every connector (0.2dB typical) Fiber Optic Distributed Data Interface (FDDI) Rated Lifetime limited warranty (Worldwide)
SIDEA CONNECTOR1	LC DUPLEX (MALE)
SIDEB CONNECTOR1	LC DUPLEX (MALE)
TECHNOLOGY	Multimode
OPERATING HUMIDITY	5% to 85% RH, Non- Condensing
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE HUMIDITY RANGE	35% to 65% RH, Non- Condensing
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
BEND RADIUS - MIN	20 mm (Dynamic); 10 mm (Static)
CLAD DIAMETER	125
CORE DIAMETER - MAX	62.5
INSERTION LOSS	≤ 0.20 dB
NUMBER OF FIBERS	2
FIBER CABLE LENGTH	61M (200 ft)

CONNECTOR GROUP	LC
CONNECTOR	LC duplex (male)
ATTENUATION 850NM	3.0 dB/km
ENDFACE POLISH	PC
OPTICAL MODE	OM1
FIBER TYPE	62.5/125
