



□□□□

Eaton NEXI1HIACGLIP

Eaton NexiTech LED, Exit sign with Increased Affordance, 20m viewing distance, Escape route, CGLine + technology, LED, Maintained / Non-Maintained operation, IP65, 80lm, 1 hour duration

□□□□

PRODUCT NAME	Eaton NexiTech LED SC Emergency Luminaire
CATALOG NUMBER	NEXI1HIACGLIP
PRODUCT LENGTH/DEPTH	308 mm
PRODUCT HEIGHT	53 mm
PRODUCT WIDTH	125 mm
PRODUCT WEIGHT	0.766 kg
CERTIFICATIONS	CE



Powering Business Worldwide

□□□□

BATTERY QUALITY	NiCd
PROTECTION CLASS	II
DEGREE OF PROTECTION	IP65
LAMP TYPE	LED not exchangeable
WITH LIGHT SOURCE	True
LAMP HOLDER	None
TYPE OF INDICATOR	Only single-sided
MONITORING EQUIPMENT	Safety module for monitoring (central feeded system)
POWER SUPPLY SYSTEM	Peripheral (individual battery)
VOLTAGE TYPE	AC
POWER FACTOR	0.41
WIRING SYSTEM	Continuous circuit/emergency circuit
WITH REMOTE SWITCH CONNECTION	True
ENERGY EFFICIENCY CLASS	A
CONDUCTOR CROSS SECTION	2.5
CONNECTION TYPE	Plug-in connection
MAX. SYSTEM POWER	3.9 W
RATED LIFE TIME L80/B10 AT 25 °C	70000 hour
TYPE OF CONTROL GEAR	LED operating device current-controlled
TYPE OF WIRING	Through wiring included
NOMINAL VOLTAGE AC - MAX	240 V
NOMINAL VOLTAGE AC - MIN	220 V
RATED AMBIENT TEMP ACC. IEC62722-2-1 - MIN	5 °C
RATED AMBIENT TEMP ACC. IEC62722-2-1 - MAX	30 °C
NOMINAL OPERATION TIME - MIN	1 hour
NOMINAL OPERATION TIME - MAX	1 hour
SUITABLE FOR STANDBY SWITCHING	No
SUITABLE FOR CONTINUOUS CIRCUIT	No
MOUNTING METHOD	Surface

□□

	mounting/recessed mounting
MATERIAL HOUSING	Plastic
COLOR HOUSING	White
MATERIAL COVER	Plastic, transparent
LABELLING TYPE	Insert sheet/plate
PICTOGRAM INCLUDED	True
BUILT-IN LENGTH	272 mm
BUILT-IN WIDTH	95 mm
BUILT-IN HEIGHT/DEPTH	96 mm
NUMBER OF POLES (NUMERIC)	2
IMPACT STRENGTH	IK07
RATED LUMINOUS FLUX ACC. IEC 62722-2-1	80 lm
COLOR TEMPERATURE - MAX	5053 K
COLOR TEMPERATURE - MIN	5053 K
LIGHT DISTRIBUTOR	Reflector
ENERGY EFFICIENCY CLASS OF THE BUILT-IN LAMP	A++, A+, A (LED)
FUNCTION	Escape route signage
LUMINAIRE WITH LIMITED SURFACE TEMPERATURE, SIGN D	False
LUMINOUS FLUX IN STANDBY MODE	80 lm
NUMBER OF LIGHTING HEADS	48
SUITABLE FOR NUMBER OF LAMPS	1
VIEWING DISTANCE	20 m
WITH REMOTE CONTROL	No
CONSTANT LIGHT OUTPUT (CLO)	No
EXCHANGEABLE CONTROL GEAR	No

